

## THM WO 50.8/150 BL

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



Similar to illustration

THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

### General ordering data

Version	THM, Conductor and cable markers, 39.7 mm, 50.8 x 150 mm, blue
Order No.	<a href="#">1109190000</a>
Type	THM WO 50.8/150 BL
GTIN (EAN)	4032248885626
Qty.	1 pc(s).

## THM WO 50.8/150 BL

Weidmüller Interfaces GmbH &amp; Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	0.025 mm	Depth (inches)	0.001 inch
Height	50.8 mm	Height (inches)	2 inch
Width	150 mm	Width (inches)	5.905 inch
Net weight	610 g		

## Temperatures

Operating temperature range	-40...125 °C
-----------------------------	--------------

## General data

Adhesive	Polyacrylate adhesive	Colour	blue
Halogen	No	Material	Polyester film
Material colour according to resistance code	6	Number of markers per combination	1 Label reel = Conductor and cable markers
Number per roll	500	Operating temperature range	-40...125 °C
Operating temperature range, max.	125 °C	Operating temperature range, min.	-40 °C
Size of labelling field	25.4 x 50.8 mm	Type of printing	neutral
UL 94 flammability rating	V-0	Version	Self-adhesive
Width	150 mm		

## Conductor and cable markers

Conductor O.D.	39.7 mm	Conductor O.D., max.	39.7 mm
Conductor cross-section, max.	500 mm <sup>2</sup>	Conductor cross-section, min.	0.75 mm <sup>2</sup>
Cross-section for connected wire	0.75 - 500 mm <sup>2</sup>	Halogen	No
Text field height	25.4 mm	Text field width	50.8 mm

## Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-04-01	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02	ECLASS 12.0	27-28-11-02

## Approvals

ROHS	Conform
------	---------

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD, EPLAN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**Data sheet**

**THM WO 50.8/150 BL**

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

