

**W-Series**  
**WEW 35/2 SW**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Product image****Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

**General ordering data**

|            |                            |
|------------|----------------------------|
| Type       | WEW 35/2 SW                |
| Order No.  | <a href="#">1061210000</a> |
| Version    | W-Series, End bracket      |
| GTIN (EAN) | 4032248136278              |
| Qty.       | 100 pc(s).                 |

**W-Series**  
**WEW 35/2 SW**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data****Dimensions and weights**

|            |        |                 |            |
|------------|--------|-----------------|------------|
| Width      | 8 mm   | Width (inches)  | 0.315 inch |
| Height     | 56 mm  | Height (inches) | 2.205 inch |
| Depth      | 47 mm  | Depth (inches)  | 1.85 inch  |
| Net weight | 14.3 g |                 |            |

**Temperatures**

|                                  |        |                                  |        |
|----------------------------------|--------|----------------------------------|--------|
| Continuous operating temp., min. | -50 °C | Continuous operating temp., max. | 100 °C |
|----------------------------------|--------|----------------------------------|--------|

**Material data**

|                           |       |        |       |
|---------------------------|-------|--------|-------|
| Material                  | Wemid | Colour | black |
| UL 94 flammability rating | V-2   |        |       |

**System specifications**

|         |                   |      |       |
|---------|-------------------|------|-------|
| Version | For the terminals | Rail | TS 35 |
|---------|-------------------|------|-------|

**Additional technical data**

|                     |                 |           |                  |
|---------------------|-----------------|-----------|------------------|
| Installation advice | Direct mounting | Interlock | for screw fixing |
| Type of mounting    | when screwed in |           |                  |

**Conductors for clamping (rated connection)**

|                         |      |                         |        |
|-------------------------|------|-------------------------|--------|
| Tightening torque, max. | 1 Nm | Tightening torque, min. | 0.5 Nm |
|-------------------------|------|-------------------------|--------|

**Dimensions**

|              |       |
|--------------|-------|
| TS 35 offset | 28 mm |
|--------------|-------|

**Classifications**

|             |             |            |             |
|-------------|-------------|------------|-------------|
| ETIM 6.0    | EC001041    | ETIM 7.0   | EC001041    |
| eClass 9.0  | 27-14-11-35 | eClass 9.1 | 27-14-11-35 |
| eClass 10.0 | 27-14-11-35 |            |             |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|                    |  |
|--------------------|--|
| Brochure/Catalogue | <a href="#">CAT 4.2 ELECTR 18/19 EN</a><br><a href="#">CAT 1 TERM 16/17 EN</a> |
| Engineering Data   | <a href="#">EPLAN, WSCAD, Zuken E3.S</a>                                       |
| Engineering Data   | <a href="#">STEP</a>   |
| User Documentation | <a href="#">StorageConditionsTerminalBlocks</a>                                |