

**Accessories**  
**VGM40-SS68 20-32 BG**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



With blueglobe®, Weidmüller has introduced a cable gland from Pflitsch into its portfolio that convinces both in terms of reliability and functionality.

A large sealing range from 1.5 to 77 mm thanks to removable inlets with just 11 cable glands, highly effective sealing, excellent strain relief and a groove-guided upstream O-ring – these are the features of the blueglobe® cable glands which Weidmüller offers in brass and stainless steel.

The heart of the blueglobe® cable gland is the spherical seal insert that squeezes the cable gently and over a large area. This permanently avoids the incisive notch effect that is common with lamella systems.

**General ordering data**

Type	VGM40-SS68 20-32 BG
Order No.	<a href="#">1193590000</a>
Version	Heavy-duty connectors, Accessories, Cable glands, Stainless steel 1.4305 (303)
GTIN (EAN)	4032248976614
Qty.	10 pc(s).

**Data sheet**

**Accessories**  
**VGM40-SS68 20-32 BG**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Technical data**

**Dimensions and weights**

Length	43 mm	Length (inches)	1.693 inch
Net weight	168 g		

**Temperatures**

Limit temperature	-40 °C ... 130 °C
-------------------	-------------------

**General data**

AF size	45 mm	Cable diameter, max.	32 mm
Cable diameter, min.	20 mm	Cable glands	M 40
External thread	M 40	Length of thread	8 mm
Material	Stainless steel 1.4305 (303)	O-Ring	Silicone
Protection degree	IP68 - 15 bar	Sealing material	T80s
Tightening torque, max.	20 Nm	Type of sealing	Rubber ring
UL 94 flammability rating	V-0		

**Classifications**

ETIM 6.0	EC000441	ETIM 7.0	EC000441
eClass 9.0	27-14-44-32	eClass 9.1	27-14-44-32
eClass 10.0	27-14-44-32		

**Approvals**

Approvals



ROHS Conform

**Downloads**

Brochure/Catalogue	<a href="#">CAT 3 HDC 17/18 EN</a> <a href="#">CAT 5 ENCL 17/18 EN</a> <a href="#">FL FIELDWIRING EN</a>
Engineering Data	<a href="#">EPLAN</a>
Engineering Data	<a href="#">STEP</a>