

**SAK Series
AP DK4Q**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image

Similar to illustration

Klippon® Connect with clamping yoke Technology

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

General ordering data

| | |
|------------|---|
| Type | AP DK4Q |
| Order No. | 1397160000 |
| Version | SAK Series, End plate, 1.5 mm, beige, Direct mounting |
| GTIN (EAN) | 4008190125899 |
| Qty. | 20 pc(s). |

Creation date August 18, 2020 4:43:46 AM CEST

Catalogue status 14.08.2020 / We reserve the right to make technical changes.

SAK Series
AP DK4Q

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

| | | | |
|------------|---------|-----------------|------------|
| Width | 1.5 mm | Width (inches) | 0.059 inch |
| Height | 54 mm | Height (inches) | 2.126 inch |
| Depth | 43.5 mm | Depth (inches) | 1.713 inch |
| Net weight | 2.8 g | | |

Temperatures

| | | | |
|----------------------------------|----------------|----------------------------------|--------|
| Storage temperature, max. | 55 °C | Storage temperature, min. | -25 °C |
| Storage temperature | -25 °C...55 °C | Continuous operating temp., min. | -50 °C |
| Continuous operating temp., max. | 100 °C | | |

Material data

| | | | |
|---------------------------|-------|--------|-------|
| Material | PA 66 | Colour | beige |
| UL 94 flammability rating | V-2 | | |

System specifications

| | |
|---------|-----------|
| Version | End plate |
|---------|-----------|

Additional technical data

| | | | |
|---------------------|-----------------|---------|-----|
| Installation advice | Direct mounting | Snap-on | Yes |
|---------------------|-----------------|---------|-----|

Classifications

| | | | |
|------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000886 | ETIM 7.0 | EC000886 |
| eClass 9.1 | 27-14-11-33 | eClass 10.0 | 27-14-11-33 |
| UNSPSC | 30-21-18-27 | | |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|--------------------|---|
| Engineering Data | EPLAN, WSCAD |
| Engineering Data | STEP |
| User Documentation | StorageConditionsTerminalBlocks |