

**KSPMH M32 BSC****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

Version	KSPMH (Klippon blanking plug, type MH), Blanking plug, in closed state, M 32, 16 mm, Brass
Order No.	<a href="#">1477780000</a>
Type	KSPMH M32 BSC
GTIN (EAN)	4050118285765
Qty.	10 pc(s).

Creation date December 21, 2022 4:53:09 PM CET

Catalogue status 16.12.2022 / We reserve the right to make technical changes.

## KSPMH M32 BSC

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

Length	21 mm	Length (inches)	0.827 inch
Diameter	32 mm	Wall thickness, max.	15 mm
Net weight	151 g		

### Temperatures

Operating temperature	-60 °C...200 °C
-----------------------	-----------------

### Certificate numbers cable gland

Approval conditions	ATEX, IECEx, EAC	Certificate no. cable gland (ATEX)	SIRA 09ATEX1320X or CML 19ATEX1089X
Certificate no. cable gland (EAC)	TR RU -GB.ГБ06.B.00098 or TR RU C- GB.BH02.B.00693-18	Certificate no. cable gland (IECEX)	IECEX SIR 09.0131X or IECEX CML 19.0022X
Identification	Ex d IIC Gb, Ex e IIC Gb, Ex tb IIIC Db		

## KSPMH M32 BSC

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

### General information

Diameter of sealing ring	32 mm	External thread	M 32
Halogen	halogen-free	Impact resistance	7 J ATEX version
Length of thread	16 mm	Material	Brass
Note: protection class	<ul style="list-style-type: none"> <li>• All metric sealing plugs have a thread pitch of 1.5 mm. • In Ex nR applications, the KSPMH must be fitted with a further seal. • To obtain the specified IP rating, the through hole must comply with the regulations of EN 50262 Table 1 and it should be possible to secure the sealing plug in a suitable manner. • Operating instructions are enclosed with each sealing plug; these must be read prior to installation. The sealing plugs must be installed according to the specifications in the operating instructions. • On installation of the KSPMH, the minimum number of engaged thread turns in line with the standard EN/IEC 60079-1, Section 5.3, must be observed. • With NEC / CEC applications, it must be ensured that the inner thread of the connection device into which the sealing plugs are screwed reveals at least 8 fully engaged thread turns. • If KSPMH sealing plugs are inserted into non-metallic Ex e connection devices, they must be connected to the system's earth circuit.</li> </ul>		
O.D.	37.5 mm	Operating temperature range, max.	Silicone 200 °C
Operating temperature range, min.	-60 °C	Protection degree	IP66, IP68 (100 m / 168 h)
Silicone	Yes	Standards	EN 60079-31, EN 60079-0, EN 60079-1, EN 60079-7
Tightening torque	10 Nm	Water depth	100 m

### Classifications

ETIM 6.0	EC000451	ETIM 7.0	EC000451
ETIM 8.0	EC000451	ECLASS 9.0	27-14-44-25
ECLASS 9.1	27-14-44-35	ECLASS 10.0	27-14-44-25
ECLASS 11.0	27-14-44-25	ECLASS 12.0	27-14-08-05

**Data sheet**

**KSPMH M32 BSC**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	8dcc5b23-3a47-4c75-bd2c-bcb18becee86

**Approvals**

Approvals



ROHS	Conform
------	---------

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>