

**SAIB-3+PE/11-S-COD****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Your peripheral devices should be supplied with greater power. With our new M12 plug-in connector, more than 250 V and 2 A is possible without problems. The compact S- and T-coded M12 plug-in connectors are designed for the transmission of up to 630 V AC or 60 V DC and 12 A.

**General ordering data**

Type	SAIB-3+PE/11-S-COD
Order No.	<a href="#">1392000000</a>
Version	Sockets prefabricated to customer spec., M12, Female socket, straight
GTIN (EAN)	4050118192360
Qty.	1 pc(s).

**SAIB-3+PE/11-S-COD****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Technical data****Dimensions and weights**

Net weight 27 g

**Temperatures**

Operating temperature, max. 85 °C Operating temperature, min. -40 °C

**Technical data customisable plug-in connectors**

Cable diameter, max.	10 mm	Cable diameter, min.	8 mm
Cable gland	PG 11	Coding	S
Connection cross-section, max.	1.5 mm <sup>2</sup>	Connection cross-section, min.	0.5 mm <sup>2</sup>
Contact surface	Gold-plated	Housing main material	PA
Insulation resistance	10 <sup>8</sup> Ω	No. of poles	4
Plugging cycles	≥ 100	Pollution severity	3
Protection degree	IP67	Rated current	12 A
Rated voltage	630 V	Shield connection	No
Temperature range of housing	-40 ... +85 °C	Threaded ring material	Diecast zinc
Type of connection	Screw connection		

**Standards**

Certificate No. (cURus) E307231

**Classifications**

ETIM 5.0	EC002635	ETIM 6.0	EC002062
eClass 6.2	27-26-07-02	eClass 7.1	27-44-01-02
eClass 8.1	27-44-01-02	eClass 9.0	27-44-01-02
eClass 9.1	27-44-01-03		

**Approvals**

Approvals



ROHS Conform

**Downloads**Brochure/Catalogue [CAT 8 SAI 15/16 EN](#)  
[FL FIELDWIRING EN](#)

**Data sheet**

**SAIB-3+PE/11-S-COD**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Drawings**

**Pole scheme**

