

HSS-HF 12.7-25.4EL Y10M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

General ordering data

Version	Conductor and cable markers, 12.7 - 25.4 mm, yellow
Order No.	1423290000
Type	HSS-HF 12.7-25.4EL Y10M
GTIN (EAN)	4050118227710
Qty.	1 pc(s).
compatible printer	2599430000 2599440000

Creation date May 18, 2023 2:19:59 PM CEST

Catalogue status 12.05.2023 / We reserve the right to make technical changes.

HSS-HF 12.7-25.4EL Y10M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	1.5 mm	Depth (inches)	0.059 inch
Width	40.5 mm	Width (inches)	1.594 inch
Length	10,000 mm	Length (inches)	393.7 inch
Net weight	570 g		

Temperatures

Operating temperature range	-55...105 °C
-----------------------------	--------------

General data

Colour	yellow	Halogen	No
Length	10,000 mm	Material	Polyolefine
Number per roll	1	Operating temperature range	-55...105 °C
Operating temperature range, max.	105 °C	Operating temperature range, min.	-55 °C
Printed characters	without	Type of printing	neutral
Width	40.5 mm		

Conductor and cable markers

Conductor O.D.	12.7 - 25.4 mm	Conductor O.D., max.	25.4 mm
Conductor O.D., min.	12.7 mm	Conductor cross-section, max.	120 mm ²
Conductor cross-section, min.	35 mm ²	Cross-section for connected wire	35 - 120 mm ²
Halogen	No	Rate of shrinkage	2:1
Recommended shrinking temperature	90 °C	Text field height	40.3 mm
Text field width	0 mm		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-04-01	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02	ECLASS 12.0	27-28-11-02

Approvals

ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	NFX 70-100-1 2006 + NF X 70-100-2 2006 BS EN ISO 4589-2 1999 EN 45545-2:2020
Engineering Data	WSCAD, EPLAN
Catalogues	Catalogues in PDF-format

Data sheet

HSS-HF 12.7-25.4EL Y10M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

