

CB1,6R18-16 SN I2,5
Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com


For a reliable contact - CB/CS crimp contact.

The combination of RSV housings and Weidmüller's crimp contacts enable custom adaptations to the specific requirements of your applications.

The following product options are available depending on the system:

- Safe centring of the contacts using the three-segment pin tips
- High contact reliability using four defined contact points
- Locking clasp in the cantilever spring for a secure mount of the contacts in the housing
- Pin contacts with two lengths to implement leading-pin contacts
- Up to 100 plugging cycles (tin version)
- Up to 500 plugging cycles (gold version)

The appropriate high-quality tools from Weidmüller guarantee professional processing.

General ordering data

| | |
|--------------|--|
| Type | CB1,6R18-16 SN I2,5 |
| Order No. | 1427800000 |
| Version | PCB plug-in connector, Crimp contact, Reel packaged, Socket, tinned, Max. clamping range : 1.5 mm ² |
| GTIN (EAN) | 4008190178086 |
| Qty. | 5,000 pc(s). |
| Product data | UL: |
| Packaging | Reel |

CB1,6R18-16 SN I2,5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight 0.63 g

System parameters

| | | | |
|------------------------|------------------|------------------|------|
| Wire connection method | Crimp connection | No. of poles | 1 |
| Volume resistance | 3.30 mΩ | Stripping length | 4 mm |
| Packaging | Reel | | |

Material data

| | | | |
|---------------------------------------|--------|---------------------------------------|--------|
| Contact material | CuZn | Contact surface | tinned |
| Storage temperature, min. | -25 °C | Storage temperature, max. | 55 °C |
| Max. relative humidity during storage | 80 % | Operating temperature, min. | -50 °C |
| Operating temperature, max. | 100 °C | Temperature range, installation, min. | -25 °C |
| Temperature range, installation, max. | 100 °C | | |

Conductors suitable for connection

| | | | |
|---|----------------------|---|---------------------|
| Clamping range, min. | 0.75 mm ² | Clamping range, max. | 1.5 mm ² |
| Wire connection cross section AWG, min. | AWG 18 | Wire connection cross section AWG, max. | AWG 16 |
| Outer diameter of insulation, min. | 2 mm | Outer diameter of insulation, max. | 2.5 mm |

Rated data acc. to IEC

tested acc. to standard IEC 60664-1, IEC 61984

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 3.0 | EC001284 | ETIM 4.0 | EC000796 |
| ETIM 5.0 | EC000796 | ETIM 6.0 | EC002943 |
| UNSPSC | 30-21-19-23 | eClass 5.1 | 27-26-12-02 |
| eClass 6.2 | 27-26-12-02 | eClass 7.1 | 27-44-02-04 |
| eClass 8.1 | 27-44-02-04 | eClass 9.0 | 27-44-02-04 |
| eClass 9.1 | 27-44-04-92 | | |

Notes

| | |
|----------------|--|
| Notes | • The long pins can be used with the standard pins as leading contacts. |
| IPC conformity | The products are developed, manufactured and delivered according to the internationally recognised IPC-A-610 standard, category "permissible". More extensive demands on the products can be evaluated on request. |

Approvals

Approvals



ROHS Conform

Data sheet**CB1,6R18-16 SN I2,5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Downloads**Approval/Certificate/Document of
Conformity[Declaration of the Manufacturer](#)

Brochure/Catalogue

[MB DEVICE MANUF. EN](#)[CAT 2 PORTFOLIOGUIDE EN](#)[FL 72H SAMPLE SER EN](#)[PO OMNIMATE EN](#)

Data sheet**CB1,6R18-16 SN I2,5**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings**Dimensional drawing**