

**Z-series  
ZAP/TW ZPV1.5**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Product image****Signal wiring**

Tailored and particularly compact: with our AIO initiator/actuator terminal blocks, you are relying on an application-optimised solution for signal wiring. We also offer you other terminal blocks featuring spring and screw connection technology for signal wiring.

**General ordering data**

| Type       | ZAP/TW ZPV1.5                         |
|------------|---------------------------------------|
| Order No.  | <a href="#">1674650000</a>            |
| Version    | Z-series, End plate, Separation plate |
| GTIN (EAN) | 4008190442576                         |
| Qty.       | 50 pc(s).                             |

**Z-series**  
**ZAP/TW ZPV1.5**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**
**Dimensions and weights**

|            |          |                 |            |
|------------|----------|-----------------|------------|
| Width      | 5.08 mm  | Width (inches)  | 0.2 inch   |
| Height     | 67.8 mm  | Height (inches) | 2.669 inch |
| Depth      | 38.35 mm | Depth (inches)  | 1.51 inch  |
| Net weight | 5.181 g  |                 |            |

**Temperatures**

|                                  |               |                                  |        |
|----------------------------------|---------------|----------------------------------|--------|
| Storage temperature, max.        | 40 °C         | Storage temperature, min.        | 10 °C  |
| Storage temperature              | 10 °C...40 °C | Continuous operating temp., min. | -50 °C |
| Continuous operating temp., max. | 120 °C        |                                  |        |

**Material data**

|                           |       |        |            |
|---------------------------|-------|--------|------------|
| Material                  | Wemid | Colour | dark beige |
| UL 94 flammability rating | V-0   |        |            |

**System specifications**

|         |                            |      |       |
|---------|----------------------------|------|-------|
| Version | End and intermediate plate | Rail | TS 35 |
|---------|----------------------------|------|-------|

**Additional technical data**

|                     |                 |         |     |
|---------------------|-----------------|---------|-----|
| Installation advice | Direct mounting | Snap-on | Yes |
|---------------------|-----------------|---------|-----|

**Dimensions**

|              |       |
|--------------|-------|
| TS 35 offset | 34 mm |
|--------------|-------|

**Classifications**

|             |             |            |             |
|-------------|-------------|------------|-------------|
| ETIM 6.0    | EC000886    | ETIM 7.0   | EC000886    |
| eClass 9.0  | 27-14-11-92 | eClass 9.1 | 27-14-11-33 |
| eClass 10.0 | 27-14-11-92 | UNSPSC     | 30-21-18-27 |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|                    |                                                 |
|--------------------|-------------------------------------------------|
| Brochure/Catalogue | <a href="#">CAT 1 TERM 16/17 EN</a>             |
| Engineering Data   | <a href="#">EPLAN, WSCAD</a>                    |
| Engineering Data   | <a href="#">STEP</a>                            |
| User Documentation | <a href="#">StorageConditionsTerminalBlocks</a> |