

**VG MS ZE (standard brass cable gland strain relief)  
VG 21-MS54-ZE**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



Cable gland with external concentric strain relief  
(clamping jaws), IP 54

**General ordering data**

Type	VG 21-MS54-ZE
Order No.	<a href="#">1718850000</a>
Version	VG MS ZE (standard brass cable gland strain relief), Cable glands, PG 21, 7 mm, OD min. 9 - OD max. 19 mm, IP65, Brass, nickel-plated
GTIN (EAN)	4008190352073
Qty.	50 pc(s).

Creation date August 22, 2020 12:23:58 PM CEST

Catalogue status 14.08.2020 / We reserve the right to make technical changes.

**VG MS ZE (standard brass cable gland strain relief)  
VG 21-MS54-ZE**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data****Dimensions and weights**

Length	38 mm	Length (inches)	1.496 inch
Net weight	92.2 g		

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
------------	----------------

**General information**

Material	Brass, nickel-plated	Cable glands	PG
External thread	PG 21	Length of thread	7 mm
AF size 1	34 mm	AF size 2	30 mm
Protection degree	IP54	Protection degree with GWDR	IP65
Operating temperature range, min.	-20 °C	Operating temperature range, max.	80 °C
Outer cable diameter, min.	9 mm	Outer cable diameter, max.	19 mm
Clamping range, strain relief, min.	12 mm	Clamping range, strain relief, max.	21 mm
Halogen	No	Seal insert	NBR
Torque for cap nut, min.	6.7 Nm	Torque for cap nut, max.	6.7 Nm
Torque for connecting adapter, min.	10 Nm	Torque for connecting adapter, max.	10 Nm

**Classifications**

ETIM 6.0	EC000441	ETIM 7.0	EC000441
eClass 9.0	27-14-44-32	eClass 9.1	27-14-44-32
eClass 10.0	27-14-44-32	UNSPSC	30-21-18-01

**Approvals**

Approvals



ROHS Conform

**Downloads**

Brochure/Catalogue	<a href="#">CAT 3 HDC 17/18 EN</a> <a href="#">CAT 5 ENCL 17/18 EN</a>
Engineering Data	<a href="#">EPLAN_WSCAD</a>