

**Cable glands  
VG M20-EXI BL**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



Cable glands that may be used for ATEX applications

**General ordering data**

Order No.	<a href="#">1737360000</a>
Type	VG M20-EXI BL
Version	Cable glands, Cable gland, Polyamide, External thread: M 20 x 1.5, Miscellaneous: Not specified
GTIN (EAN)	4008190956837
Qty.	20 pc(s).

**Cable glands  
VG M20-EXI BL**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Technical data**

**Dimensions and weights**

Length	35 mm	Net weight	8.4 g
--------	-------	------------	-------

**Approvals**

Approval for cable gland	Ex i II, II 2 GD
--------------------------	------------------

**General information**

AF size 1	24 mm	Cable gland	metric
Clamp insert	Polyamide	Clamping range, bolted connection , max.	13 mm
Clamping range, min. test adapter	8 mm	Colour code	RAL 5012
External thread	M 20 x 1.5	Length of thread	10 mm
Material	Polyamide	Operating temperature range, max.	80 °C
Operating temperature range, min.	-20 °C	Pitch of thread	1.5 mm
Protection degree with GWDR	IP 68	Seal insert	TPE
Torque for cap nut, max.	3 Nm	Torque for cap nut, min.	3 Nm
Torque for connecting adapter, max.	3 Nm	Torque for connecting adapter, min.	3 Nm
UL 94 flammability rating	V-2		

**Classifications**

ETIM 2.0	EC000441	ETIM 3.0	EC000441
UNSPSC	30-21-18-01	eClass 4.1	27-14-12-11
eClass 5.1	27-14-91-11	eClass 6.0	27-14-91-11
eClass 7.0	27-14-91-11		

**Approvals**

Approvals

