

**VG K (standard plastic cable gland)
VG M20-1/K68**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Screwed joints that comply with the high demands of class of protection IP 68

General ordering data

Type	VG M20-1/K68
Order No.	1772300000
Version	VG K (standard plastic cable gland), Cable glands, M 20, 10 mm, OD min. 6 - OD max. 12 mm, IP54, IP66, IP67, IP68 - 5 bar (30 min.), Polyamide 6
GTIN (EAN)	4032248129966
Qty.	50 pc(s).

Creation date August 15, 2020 11:17:40 PM CEST

Catalogue status 24.07.2020 / We reserve the right to make technical changes.

**VG K (standard plastic cable gland)
VG M20-1/K68**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data
Dimensions and weights

Length	39.5 mm	Length (inches)	1.555 inch
Net weight	10.3 g		

Certificate numbers cable gland

Approval conditions	DNV, UL, cULus	Certificate no. cable gland (CSA)	115116
Certificate no. cable gland (GERMLLOYD)	E-14046	Certificate no. cable gland (UL)	E-199260
Certificate no. cable gland (cULus)	E-199260		

General information

Material	Polyamide 6	Cable glands	metric
External thread	M 20	Pitch of thread	1.5 mm
Length of thread	10 mm	AF size 1	24 mm
Protection degree	IP67, IP68 - 5 bar (30 min.)	Protection degree with GWDR	IP54, IP66, IP67, IP68 - 5 bar (30 min.)
Operating temperature range, min.	-40 °C	Operating temperature range, max.	100 °C
Outer cable diameter, min.	6 mm	Outer cable diameter, max.	12 mm
UL 94 flammability rating	V-2	Halogen	Yes
Seal insert	CR	Tightening torque	3.5 Nm
Torque for cap nut, min.	5 Nm	Torque for cap nut, max.	6 Nm
Torque for connecting adapter, min.	5 Nm	Torque for connecting adapter, max.	6 Nm
Torque for lock nut, min.	5 Nm	Torque for lock nut, max.	6 Nm
Standards	EN/IEC 62444	Note: protection class	IP66 applications only possible with sealing ring for threaded connections. Without sealing ring for threaded connections, only IP54 is possible.

Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
eClass 9.0	27-14-44-32	eClass 9.1	27-14-44-32
eClass 10.0	27-14-44-32	UNSPSC	30-21-18-01

Approvals

Approvals



ROHS Conform

Downloads

Brochure/Catalogue	CAT 3 HDC 17/18 EN CAT 5 ENCL 17/18 EN
Engineering Data	EPLAN.WSCAD