

**EWS (drainage device)
EWS M 25X1,5**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Pressure-compensation elements ensure good ventilation of the enclosure and prevent the build-up of condensation while maintaining the appropriate IP class of protection.

General ordering data

Type	EWS M 25X1,5
Order No.	1719740000
Version	EWS (drainage device), Compensating element, M 25, 5 mm, Polyamide
GTIN (EAN)	4008190353001
Qty.	20 pc(s).

Data sheet

**EWS (drainage device)
EWS M 25X1,5**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Length	23 mm	Length (inches)	0.906 inch
Net weight	13.25 g		

General information

AF size 1	30 mm	Cable glands	metric
External thread	M 25	Length of thread	5 mm
Material	Polyamide	Operating temperature range, max.	40 °C
Operating temperature range, min.	-20 °C	Pitch of thread	1.5 mm
Protection degree	IP54	Torque for connecting adapter, max.	5 Nm
Torque for connecting adapter, min.	5 Nm	UL 94 flammability rating	V-2

Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
eClass 9.0	27-14-44-32	eClass 9.1	27-14-44-90
eClass 10.0	27-14-44-32	UNSPSC	30-21-18-01

Approvals

Approvals



ROHS Conform

Downloads

Engineering Data	EPLAN, WSCAD
Engineering Data	STEP

Data sheet

**EWS (drainage device)
EWS M 25X1,5**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

