

**Z-series  
ZDU 1.5 OR**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Product image****Spring connection with tension clamp Technology**

Tension clamp technology is a universal contact system for all common conductor connection types. Its fantastic level of flexibility makes the tension clamp a profitable alternative connection.

**General ordering data**

|            |                                                                                 |
|------------|---------------------------------------------------------------------------------|
| Type       | ZDU 1.5 OR                                                                      |
| Order No.  | <a href="#">1775500000</a>                                                      |
| Version    | Feed-through terminal, Tension-clamp connection, 1.5 mm², 500 V, 17.5 A, orange |
| GTIN (EAN) | 4032248181483                                                                   |
| Qty.       | 100 pc(s).                                                                      |

**Z-series**  
**ZDU 1.5 OR**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**
**Dimensions and weights**

|                          |         |                 |            |
|--------------------------|---------|-----------------|------------|
| Width                    | 3.5 mm  | Width (inches)  | 0.138 inch |
| Height                   | 51.5 mm | Height (inches) | 2.028 inch |
| Depth                    | 36.5 mm | Depth (inches)  | 1.437 inch |
| Depth including DIN rail | 37 mm   | Net weight      | 4.64 g     |

**Temperatures**

|                                  |                                                                                                   |                                  |               |
|----------------------------------|---------------------------------------------------------------------------------------------------|----------------------------------|---------------|
| Operating temperature range      | For operating temperature range see EC Design Test Certificate / IEC Ex-Certificate of Conformity | Storage temperature, max.        | 40 °C         |
| Storage temperature, min.        | 10 °C                                                                                             | Storage temperature              | 10 °C...40 °C |
| Continuous operating temp., min. | -50 °C                                                                                            | Continuous operating temp., max. | 120 °C        |

**Material data**

|                           |       |        |        |
|---------------------------|-------|--------|--------|
| Material                  | Wemid | Colour | orange |
| UL 94 flammability rating | V-0   |        |        |

**Rating data IECEx/ATEX**

|                                |                                                                                                   |                                 |                     |
|--------------------------------|---------------------------------------------------------------------------------------------------|---------------------------------|---------------------|
| Certificate No. (ATEX)         | KEMA01ATEX2106U                                                                                   | Certificate No. (IECEX)         | IECEXULD15.0008U    |
| Max. voltage (ATEX)            | 550 V                                                                                             | Current (ATEX)                  | 15 A                |
| Wire cross section max. (ATEX) | 1.5 mm <sup>2</sup>                                                                               | Max. voltage (IECEX)            | 550 V               |
| Current (IECEX)                | 17 A                                                                                              | Wire cross section max. (IECEX) | 1.5 mm <sup>2</sup> |
| Operating temperature range    | For operating temperature range see EC Design Test Certificate / IEC Ex-Certificate of Conformity | Marking EN 60079-7              | Ex eb II C Gb       |
| Ex 2014/34/EU label            | II 2 G D                                                                                          |                                 |                     |

**System specifications**

|                               |                                                                                  |                                     |       |
|-------------------------------|----------------------------------------------------------------------------------|-------------------------------------|-------|
| Version                       | Tension-clamp connection, for plug-in cross-connector, One end without connector | End cover plate required            | Yes   |
| Number of levels              | 1                                                                                | Number of clamping points per level | 2     |
| Number of potentials per tier | 1                                                                                | Levels cross-connected internally   | No    |
| PE connection                 | No                                                                               | Rail                                | TS 35 |

**Additional technical data**

|                          |       |                             |         |
|--------------------------|-------|-----------------------------|---------|
| Explosion-tested version | Yes   | Number of similar terminals | 1       |
| Open sides               | right | Type of mounting            | Snap-on |

**CSA rating data**

|                               |                |                               |        |
|-------------------------------|----------------|-------------------------------|--------|
| Certificate No. (CSA)         | 200039-1152892 | Current size C (CSA)          | 20 A   |
| Voltage size C (CSA)          | 300 V          | Wire cross section max. (CSA) | 14 AWG |
| Wire cross section min. (CSA) | 26 AWG         |                               |        |

**Z-series**  
**ZDU 1.5 OR**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**
**Conductors for clamping (rated connection)**

|                                                                                         |                      |                                                                                         |                          |
|-----------------------------------------------------------------------------------------|----------------------|-----------------------------------------------------------------------------------------|--------------------------|
| Blade size                                                                              | 0.4 x 2.0 mm         | Clamping range, max.                                                                    | 1.5 mm <sup>2</sup>      |
| Clamping range, min.                                                                    | 0.05 mm <sup>2</sup> | Connection direction                                                                    | top                      |
| Gauge to IEC 60947-1                                                                    | B1                   | Number of connections                                                                   | 2                        |
| Stripping length                                                                        | 10 mm                | Twin wire-end ferrules, max.                                                            | 0.75 mm <sup>2</sup>     |
| Twin wire-end ferrules, min.                                                            | 0.5 mm <sup>2</sup>  | Type of connection                                                                      | Tension-clamp connection |
| Wire connection cross section AWG, max.                                                 | AWG 16               | Wire connection cross section AWG, min.                                                 | AWG 16                   |
| Wire connection cross section, finely stranded, max.                                    | 1.5 mm <sup>2</sup>  | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 1.5 mm <sup>2</sup>      |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.5 mm <sup>2</sup>  | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 1.5 mm <sup>2</sup>      |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.5 mm <sup>2</sup>  | Wire connection cross-section, finely stranded, min.                                    | 0.5 mm <sup>2</sup>      |
| Wire connection cross-section, solid core, max.                                         | 1.5 mm <sup>2</sup>  | Wire connection cross-section, solid core, min.                                         | 0.5 mm <sup>2</sup>      |

**Rating data**

|                                             |                     |                                              |         |
|---------------------------------------------|---------------------|----------------------------------------------|---------|
| Rated cross-section                         | 1.5 mm <sup>2</sup> | Rated voltage                                | 500 V   |
| Rated current                               | 17.5 A              | Current at maximum wires                     | 17.5 A  |
| Standards                                   | IEC 60947-7-1       | Volume resistance according to IEC 60947-7-x | 1.83 mΩ |
| Power loss in accordance with IEC 60947-7-x | 0.56 W              | Rated impulse withstand voltage              | 6 kV    |
| Pollution severity                          | 3                   |                                              |         |

**UL rating data**

|                                         |        |                                         |        |
|-----------------------------------------|--------|-----------------------------------------|--------|
| Certificate No. (UR)                    | E60693 | Conductor size Factory wiring max. (UR) | 14 AWG |
| Conductor size Factory wiring min. (UR) | 26 AWG | Conductor size Field wiring max. (UR)   | 14 AWG |
| Conductor size Field wiring min. (UR)   | 26 AWG | Current size C (UR)                     | 15 A   |
| Voltage size C (UR)                     | 300 V  |                                         |        |

**Classifications**

|             |             |            |             |
|-------------|-------------|------------|-------------|
| ETIM 6.0    | EC000897    | ETIM 7.0   | EC000897    |
| eClass 9.0  | 27-14-11-20 | eClass 9.1 | 27-14-11-20 |
| eClass 10.0 | 27-14-11-20 | UNSPSC     | 30-21-18-11 |

**Approvals**

Approvals



CURUSEX

ATEX



IEC EX



ATEX - KEMA

ROHS

Conform

## Z-series ZDU 1.5 OR

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

|                                             |                                                                                                                                                                           |
|---------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Approval/Certificate/Document of Conformity | <a href="#">Attestation of Conformity</a><br><a href="#">IECEX Certificate</a><br><a href="#">ATEX Certificate</a><br><a href="#">DE_PT1101_20160418_1146_ISSUE01.pdf</a> |
| Engineering Data                            | <a href="#">EPLAN, WSCAD, Zuken E3.S</a>                                                                                                                                  |
| Engineering Data                            | <a href="#">STEP</a>                                                                                                                                                      |
| User Documentation                          | <a href="#">Cross Connection Guide</a><br><a href="#">StorageConditionsTerminalBlocks</a>                                                                                 |

### Safety note

|               |                                    |
|---------------|------------------------------------|
| Safety notice | <a href="#">Safety Information</a> |
|---------------|------------------------------------|

### Z-series ZDU 1.5 OR

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

