

GWDR M63-PO**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	GWDR PO (flat gasket - polyethylene), Sealing ring, M 63, Polyethylene
Order No.	1777990000
Type	GWDR M63-PO
GTIN (EAN)	4032248158256
Qty.	50 pc(s).

Creation date January 31, 2023 12:53:20 PM CET

Catalogue status 24.01.2023 / We reserve the right to make technical changes.

GWDR M63-PO

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight 1.42 g

Temperatures

Operating temperature	-30 °C...90 °C	Operating temperature, min.	-30 °C
Operating temperature, max.	90 °C		

General information

Cable glands	M 63	Diameter of sealing ring	70 mm
External thread	M 63	Inside diameter D2	63 mm
Material	Polyethylene	Number of wires	1
O.D.	70 mm	Operating temperature range, max.	90 °C
Operating temperature range, min.	-30 °C	Pitch of thread	1.5 mm
Sealing	PE-HD	Silicone	Yes
Thickness	2 mm		

Classifications

ETIM 6.0	EC001181	ETIM 7.0	EC001181
ETIM 8.0	EC001181	ECLASS 9.0	27-43-03-19
ECLASS 9.1	27-14-44-90	ECLASS 10.0	27-43-03-19
ECLASS 11.0	27-43-03-19	ECLASS 12.0	27-43-03-19

Approvals

ROHS Conform

Downloads

Engineering Data	CAD data – STEP
Engineering Data	WSCAD
Catalogues	Catalogues in PDF-format
Brochures	

Data sheet

GWDR M63-PO

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

