

**SKMU PA (plastic locknut)
SKMU M20 K SW**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Weidmüller has a variety of different cable and wire entry systems in the Portfolio: with different designs of plastic, brass and stainless steel cable glands in the IP66, 67, 68 or IP69k protection classes. As a complete alternative to cable glands, pre-assembled cables with modular multi-wire or multi-cable entry systems can be simply and quickly inserted into electrical equipment. Last but not least, Weidmüller offers EX-certified cable glands and cable/wire entry systems.

- Cable glands made from plastic and brass
- EMC screwed joints
- for areas at risk of explosion
- VDE, CSA and UL approvals

General ordering data

Type	SKMU M20 K SW
Order No.	1736930000
Version	SKMU PA (plastic locknut), Locknut, M 20, 6 mm, Polyamid 6 (PA6 - GF30)
GTIN (EAN)	4008 190956400
Qty.	100 pc(s).

Data sheet

**SKMU PA (plastic locknut)
SKMU M20 K SW**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Net weight 1.8 g

General information

Material	Polyamid 6 (PA6 - GF30)	Cable glands	metric
External thread	M 20	Pitch of thread	1.5 mm
Length of thread	6 mm	AF size 1	26 mm
Operating temperature range, min.	-40 °C	Operating temperature range, max.	100 °C
Thickness	6 mm	UL 94 flammability rating	V-2
Internal thread	M 20	Halogen	No

Classifications

ETIM 6.0	EC000940	ETIM 7.0	EC000940
eClass 9.0	27-14-44-24	eClass 9.1	27-14-44-24
eClass 10.0	27-14-44-24	UNSPSC	30-21-18-01

Approvals

Approvals



ROHS Conform

Downloads

Brochure/Catalogue	CAT 5 ENCL 17/18 EN
Engineering Data	EPLAN, WSCAD
Engineering Data	STEP

Data sheet

SKMU PA (plastic locknut)
SKMU M20 K SW

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

