

**VG MS (standard brass cable gland)
VG M16 - MS 68**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Screwed joints that comply with the high demands of class of protection IP 68

General ordering data

Type	VG M16 - MS 68
Order No.	1772210000
Version	VG MS (standard brass cable gland), Cable glands, M 16, 7 mm, OD min. 4 - OD max. 8 mm, IP54, IP66, IP67, IP68 - 5 bar (30 min.), IP69K, Brass, nickel-plated
GTIN (EAN)	4032248129867
Qty.	50 pc(s).

Creation date August 17, 2020 7:07:11 AM CEST

**VG MS (standard brass cable gland)
VG M16 - MS 68**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

Length	30 mm	Length (inches)	1.181 inch
Net weight	19.72 g		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Certificate numbers cable gland

Approval conditions	DNV, UL, cULus	Certificate no. cable gland (GERMLLOYD)	E-14047
Certificate no. cable gland (UL)	E-199260	Certificate no. cable gland (cULus)	E-199260

General information

Material	Brass, nickel-plated	Cable glands	metric
External thread	M 16	Pitch of thread	1.5 mm
Length of thread	7 mm	AF size 1	17 mm
AF size 2	18 mm	Protection degree	IP54, IP66, IP67, IP68 - 5 bar (30 min.), IP69K
Protection degree with GWDR	IP54, IP66, IP67, IP68 - 5 bar (30 min.), IP69K	Operating temperature range, min.	-40 °C
Operating temperature range, max.	100 °C	Outer cable diameter, min.	4 mm
Outer cable diameter, max.	8 mm	Halogen	No
Clamp insert	Polyamide	O-Ring	NBR
Seal insert	CR	Sealing	NBR
Tightening torque	4 Nm	Torque for cap nut, min.	5 Nm
Torque for cap nut, max.	6 Nm	Torque for connecting adapter, min.	3.5 Nm
Torque for connecting adapter, max.	4.5 Nm		

Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
eClass 9.0	27-14-44-32	eClass 9.1	27-14-44-32
eClass 10.0	27-14-44-32	UNSPSC	30-21-18-01

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 3 HDC 17/18 EN CAT 5 ENCL 17/18 EN
Engineering Data	EPLAN, WSCAD
Engineering Data	STEP