

**VG MS ZE (standard brass cable gland strain relief)
VGM25-MS54 ZE**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



Cable gland with external concentric strain relief
 (clamping jaws), IP 54

General ordering data

Type	VGM25-MS54 ZE
Order No.	1778480000
Version	VG MS ZE (standard brass cable gland strain relief), Cable glands, M 25, 7 mm, OD min. 9 - OD max. 19 mm, IP65, Brass, nickel-plated
GTIN (EAN)	4032248161492
Qty.	25 pc(s).

Creation date August 7, 2020 9:06:20 AM CEST

**VG MS ZE (standard brass cable gland strain relief)
VGM25-MS54 ZE**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data
Dimensions and weights

Length	38 mm	Length (inches)	1.496 inch
Net weight	93.9 g		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

General information

Material	Brass, nickel-plated	Cable glands	metric
External thread	M 25	Pitch of thread	1.5 mm
Length of thread	7 mm	AF size 1	34 mm
AF size 2	30 mm	Protection degree	IP54
Protection degree with GWDR	IP65	Operating temperature range, min.	-20 °C
Operating temperature range, max.	80 °C	Outer cable diameter, min.	9 mm
Outer cable diameter, max.	19 mm	Clamping range, strain relief, min.	12 mm
Clamping range, strain relief, max.	21 mm	Halogen	No
Seal insert	NBR	Torque for cap nut, min.	8 Nm
Torque for cap nut, max.	8 Nm	Torque for connecting adapter, min.	12 Nm
Torque for connecting adapter, max.	12 Nm		

Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
eClass 9.0	27-14-44-32	eClass 9.1	27-14-44-32
eClass 10.0	27-14-44-32	UNSPSC	30-21-18-01

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 3 HDC 17/18 EN CAT 5 ENCL 17/18 EN
Engineering Data	EPLAN, WSCAD