

I-Series
IAP 1.5N/4AN

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage.

It guarantees protection against contact with live parts and makes the final terminal finger-proof.

If cross-connections are shortened, end plates must be used on the bare cut edges of the cross-connection to maintain the rated voltage of 250 V.

Coloured end plates are used to distinguish different circuits.

General ordering data

Order No.	1792470000
Type	IAP 1.5N/4AN
Version	I-Series, End plate, Dark Beige, 2 mm
GTIN (EAN)	4032248283279
Qty.	50 pc(s).

I-Series
IAP 1.5N/4AN

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Length	93 mm	Width	2 mm
Height	32.5 mm	Net weight	6.401 g

Temperatures

Operating temperature		Storage temperature	
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C

Additional technical data

Installation advice	Direct mounting	Version	End plate
---------------------	-----------------	---------	-----------

DIN mounting rail

Material	Wemid	Thickness	2 mm
Installation advice	Direct mounting	Version	End plate

Material data

Material	Wemid	Colour	Dark Beige
UL 94 flammability rating	V-0		

System specifications

Product family	I-Series
----------------	----------

Classifications

ETIM 2.0	EC000886	ETIM 3.0	EC000886
UNSPSC	30-21-18-27	eClass 4.1	27-14-11-99
eClass 5.1	27-14-11-33	eClass 6.0	27-14-11-33
eClass 7.0	27-14-11-33		

Approvals

Approvals


Downloads

DXF	32897_IAP_1.5N-4AN_DXF.dxf
STEP	1792470000_32897_IAP_1.5N-4AN_STP.stp