


## OMNIMATE Signal - series BC/SC 3.81 BCZ 3.81/04/90F SN BK BX

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



Female socket connectors with clamping-yoke screw system for connecting wires.

Three wire-outlet directions are available and provide flexible connection-level design options:

- 180° wire parallel to plugging direction
- 90° wire perpendicular and above plugging direction
- 270° wire perpendicular and below plugging direction

There are three housing shapes, covering many different requirements, to choose from:

- Standard housing without flange
- Flange with screw (F)
- Flange featuring Weidmüller's patented release latch (LR) for lock-and-release latching with no strain and no tools needed.

Weidmüller's 3.81-mm-pitch (0.15 inch) plug-in connectors are compatible with the layouts of customary connectors and offer space for labelling and coding.

- 0.20 - 1.5 mm<sup>2</sup> (IEC) / 28 - 16 AWG (UL)
- 250 V (IEC) / 300 V (UL)
- 17.5 A (IEC) / 10 A (UL)

### General ordering data

Type	BCZ 3.81/04/90F SN BK BX
Order No.	<a href="#">1798790000</a>
Version	PCB plug-in connector, female plug, 3.81 mm, No. of poles: 4, 90°, Clamping yoke connection, Clamping range, rated connection, max.: 1.5 mm <sup>2</sup> , Box
GTIN (EAN)	4032248243471
Qty.	50 pc(s).
Product data	IEC: 320 V / 17.5 A / 0.2 - 1.5 mm <sup>2</sup> UL: 300 V / 10 A / AWG 28 - AWG 16
Packaging	Box

Creation date July 29, 2013 1:25:00 PM CEST

**OMNIMATE Signal - series BC/SC 3.81  
BCZ 3.81/04/90F SN BK BX**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Technical data**
**Dimensions and weights**

Net weight 4.82 g

**System parameters**

Product family	OMNIMATE Signal - series BC/SC 3.81	Wire connection method	Clamping yoke connection
Conductor outlet direction	90°	Pitch in mm (P)	3.81 mm
Pitch in inches (P)	0.15 inch	No. of poles	4
Screwdriver blade	0.4 x 2.5	Screwdriver blade standard	DIN 5264
Tightening torque, min.	0.2 Nm	Tightening torque, max.	0.25 Nm
Clamping screw	M 2	Stripping length	7 mm
L1 in mm	11.43 mm	L1 in inches	0.45 inch
Touch-safe protection acc. to DIN VDE 0470	IP 20	Touch-safe protection acc. to DIN VDE 57 106	Safe from finger touch

**Material data**

Insulating material	PA GF	Colour	Black
Colour chart (similar)	RAL 9011	UL 94 flammability rating	V-0
CTI	≥ 550	Contact material	Cu-Leg
Contact surface	tinned		

**Connectable conductors**

Clamping range, rated connection, min.	0.08 mm <sup>2</sup>	Clamping range, rated connection, max.	1.5 mm <sup>2</sup>
Wire connection cross section AWG, min.	AWG 28	Wire connection cross section AWG, max.	AWG 16
Solid, min. H05(07) V-U	0.2 mm <sup>2</sup>	Solid, max. H05(07) V-U	1.5 mm <sup>2</sup>
Flexible, min. H05(07) V-K	0.2 mm <sup>2</sup>	Flexible, max. H05(07) V-K	1.5 mm <sup>2</sup>
w. wire end ferrule, DIN 46228 pt 1, min.	0.2 mm <sup>2</sup>	w. wire end ferrule, DIN 46228 pt 1, max.	1.5 mm <sup>2</sup>
w. plastic collar ferrule, DIN 46228 pt 4, min.	0.2 mm <sup>2</sup>	w. plastic collar ferrule, DIN 46228 pt 4, max.	1.5 mm <sup>2</sup>
Plug gauge acc. to EN 60999 a x b; Ø	2.4 mm x 1.5 mm ; 2.4 mm		

**DIN IEC rating data**

Rated current, min. no. of poles (Tu=20°C)	17.5 A	Rated current, max. no. of poles (Tu=20°C)	15.9 A
Rated current, number of poles (Tu=40°C), min	17.5 A	Rated current, number of poles (Tu=40°C), max.	14.1 A
Rated voltage for surge voltage class pollution degree II/2	320 V	Rated voltage for surge voltage class pollution degree III/2	160 V
Rated voltage for surge voltage class pollution degree III/3	160 V	Rated impulse voltage for surge voltage class pollution degree II/2	2.5 kV
Rated impulse voltage for surge voltage class pollution degree III/2	2.5 kV	Rated impulse voltage for surge voltage class contamination degree III/3	2.5 kV
Short-time withstand current resistance	3 x 1s with 76 A		

**OMNIMATE Signal - series BC/SC 3.81  
BCZ 3.81/04/90F SN BK BX**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Technical data**

**CSA rating data**

Institute (CSA)



Rated voltage (Use group B)

300 V

Rated current (use group B)	10 A
Rated current (use group D)	10 A
Wire cross-section, AWG, max.	AWG 16

Rated voltage (use group D)	300 V
Wire cross-section, AWG, min.	AWG 28

**UL 1059 rating data**

Rated voltage (use group B)	300 V
Rated voltage (use group D)	300 V
Wire cross-section, AWG, min.	AWG 28

Rated current (use group B)	10 A
Rated current (use group D)	10 A
Wire cross-section, AWG, max.	AWG 16

**Classifications**

ETIM 3.0	EC001284	UNSPSC	30-21-18-10
eClass 4.1	27-26-07-01	eClass 5.1	27-26-07-04
eClass 6.2	27-26-07-04	eClass 7.1	27-44-04-02

**Notes**

Notes

- Additional colours on request
- Gold-plated contact surfaces on request
- Rated current related to rated cross-section & min. No. of poles.
- Wire end ferrule without plastic collar to DIN 46228/1
- Wire end ferrule with plastic collar to DIN 46228/4
- P on drawing = pitch
- Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.

**Approvals**

Approvals




ROHS

Conform


**OMNIMATE Signal - series BC/SC 3.81  
BCZ 3.81/04/90F SN BK BX**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com


**Drawings**




BCZ 3.81../90 & /270 - SC 3.81../135




BCZ 3.81../90 & /270 - SC-SMT 3.81../135



BCZ 3.81../90 & /270 - SC-SMT 3.81../135



BCZ 3.81../90 & /270 - SC 3.81../135



**OMNIMATE Signal - series BC/SC 3.81  
BCZ 3.81/04/90F SN BK BX**

**Weidmüller Interface GmbH & Co. KG**  
 Klängenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Mating connector (fully pluggable)**
**SC-SMT 3.81/180LF Tape**


High-temperature-resistant pin header (SC-SMT 180LF) in 3.81-mm pitch (0.15 inch)

- Plugging direction is perpendicular to PCB (standing)
- With solder flange (LF).
- Packed either in box (BX) or on anti-static roll (tape-on-reel, RL)
- Pin length of either 1.5 mm or 3.2 mm

Weidmüller's 3.81-mm-pitch (0.15 inch) plug-in connectors are compatible with the layouts of standard connectors and offer space for labelling.

- 320 V (IEC) / 300 V (UL)
- 14.9 A (IEC) / 10 A (UL)

**General ordering data**

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SC-SMT 3.81/04/180LF 1.5SN BK RL	<a href="#">1864240000</a>	PCB plug-in connector, male header, Solder flange, Reflow solder connection, 3.81 mm, No. of poles: 4, 180°, Solder pin length (l): 1.5 mm, tinned, Black, Tape	4032248429547	300 pc(s).	IEC: 320 V / 17.5 A UL: 300 V / 10 A	Tape
SC-SMT 3.81/04/180LF 3.2SN BK RL	<a href="#">1863530000</a>	PCB plug-in connector, male header, Solder flange, Reflow solder connection, 3.81 mm, No. of poles: 4, 180°, Solder pin length (l): 3.2 mm, tinned, Black, Tape	4032248428700	300 pc(s).	IEC: 320 V / 17.5 A UL: 300 V / 10 A	Tape

**SC-SMT 3.81/90LF Tape**


High-temperature-resistant pin header (SC-SMT 90LF) in 3.81-mm pitch (0.15 inch)

- Plugging direction parallel to PCB (recumbent)
- With solder flange (LF).
- Packed either in box (BX) or on anti-static roll (tape-on-reel, RL)
- Pin length of either 1.5 mm or 3.2 mm

Weidmüller's 3.81-mm-pitch (0.15 inch) plug-in connectors are compatible with the layouts of standard connectors and offer space for labelling.

- 320 V (IEC) / 300 V (UL)
- 14.9 A (IEC) / 10 A (UL)

**General ordering data**

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SC-SMT 3.81/04/90LF 3.2SN BK RL	<a href="#">1863980000</a>	PCB plug-in connector, male header, Solder flange, Reflow solder connection, 3.81 mm, No. of poles: 4,	4032248429226	400 pc(s).	IEC: 320 V / 17.5 A UL: 300 V / 10 A	Tape

**OMNIMATE Signal - series BC/SC 3.81  
BCZ 3.81/04/90F SN BK BX**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Mating connector (fully pluggable)**

SC-SMT	<a href="#">1862770000</a>	90°, Solder pin length (l): 3.2 mm, tinned, Black, Tape	4032248427963 400 pc(s).	IEC: 320 V / 17.5 A UL: 300 V / 10 A	Tape
3.81/04/90LF		PCB plug-in connector, male header, Solder flange, Reflow solder connection, 3.81 mm, No. of poles: 4, 90°, Solder pin length (l): 1.5 mm, tinned, Black, Tape			
1.5SN BK RL					

**SC-SMT 3.81/90LF Box**


High-temperature-resistant pin header (SC-SMT 90LF) in 3.81-mm pitch (0.15 inch)

- Plugging direction parallel to PCB (recumbent)
- With solder flange (LF).
- Packed either in box (BX) or on anti-static roll (tape-on-reel, RL)
- Pin length of either 1.5 mm or 3.2 mm

Weidmüller's 3.81-mm-pitch (0.15 inch) plug-in connectors are compatible with the layouts of standard connectors and offer space for labelling.

- 320 V (IEC) / 300 V (UL)
- 14.9 A (IEC) / 10 A (UL)

**General ordering data**

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SC-SMT	<a href="#">1862590000</a>	PCB plug-in connector, male header, Solder flange, Reflow solder connection, 3.81 mm, No. of poles: 4, 90°, Solder pin length (l): 1.5 mm, tinned, Black, Box	4032248427550 50 pc(s).		IEC: 320 V / 17.5 A UL: 300 V / 10 A	Box
3.81/04/90LF						
1.5SN BK BX						
SC-SMT	<a href="#">1863690000</a>	PCB plug-in connector, male header, Solder flange, Reflow solder connection, 3.81 mm, No. of poles: 4, 90°, Solder pin length (l): 3.2 mm, tinned, Black, Box	4032248428878 50 pc(s).		IEC: 320 V / 17.5 A UL: 300 V / 10 A	Box
3.81/04/90LF						
3.2SN BK BX						

**OMNIMATE Signal - series BC/SC 3.81  
BCZ 3.81/04/90F SN BK BX**

**Weidmüller Interface GmbH & Co. KG**  
 Klängenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Mating connector (fully pluggable)**
**SC-SMT 3.81/180LF Box**


High-temperature-resistant pin header (SC-SMT 180LF) in 3.81-mm pitch (0.15 inch)

- Plugging direction is perpendicular to PCB (standing)
- With solder flange (LF).
- Packed either in box (BX) or on anti-static roll (tape-on-reel, RL)
- Pin length of either 1.5 mm or 3.2 mm

Weidmüller's 3.81-mm-pitch (0.15 inch) plug-in connectors are compatible with the layouts of standard connectors and offer space for labelling.

- 320 V (IEC) / 300 V (UL)
- 14.9 A (IEC) / 10 A (UL)

**General ordering data**

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SC-SMT 3.81/04/180LF 3.2SN BK BX	<a href="#">1863260000</a>	PCB plug-in connector, male header, Solder flange, Reflow solder connection, 3.81 mm, No. of poles: 4, 180°, Solder pin length (l): 3.2 mm, tinned, Black, Box	4032248428458	50 pc(s).	IEC: 320 V / 17.5 A UL: 300 V / 10 A	Box
SC-SMT 3.81/04/180LF 1.5SN BK BX	<a href="#">1864090000</a>	PCB plug-in connector, male header, Solder flange, Reflow solder connection, 3.81 mm, No. of poles: 4, 180°, Solder pin length (l): 1.5 mm, tinned, Black, Box	4032248429295	50 pc(s).	IEC: 320 V / 17.5 A UL: 300 V / 10 A	Box

**SC 3.81/180F**


The SC pin header has a perpendicular (standing) plugging direction in relation to the PCB. It is available in closed (G) and screw flange (F) versions.

Weidmüller's 3.81-mm-pitch (0.15 inch) plug-in connectors are compatible with the layouts of standard connectors and offer space for labelling and coding.

- 320 V (IEC) / 300 V (UL)
- 17.5 A (IEC) / 10 A (UL)

**General ordering data**

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SC 3.81/04/180F 3.2SN GN BX	<a href="#">1793810000</a>	PCB plug-in connector, male header, Flange, Solder connection, 3.81 mm, No. of poles: 4, 180°, Solder pin length (l): 3.2 mm, tinned, Pale green, Box	4032248230938	50 pc(s).	IEC: 320 V / 17.5 A UL: 300 V / 10 A	Box
SC 3.81/04/180F 3.2SN OR BX	<a href="#">1943200000</a>	PCB plug-in connector, male header, Flange, Solder connection, 3.81 mm, No.	4032248654390	50 pc(s).	IEC: 320 V / 17.5 A UL: 300 V / 10 A	Box

Creation date July 29, 2013 1:25:00 PM CEST


**OMNIMATE Signal - series BC/SC 3.81  
BCZ 3.81/04/90F SN BK BX**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Mating connector (fully pluggable)**

of poles: 4, 180°, Solder pin  
length (l): 3.2 mm, tinned,  
Orange, Box

SC 3.81/04/180F 3.2SN BK BX	<a href="#">1793720000</a>	PCB plug-in connector, male header, Flange, Solder connection, 3.81 mm, No. of poles: 4, 180°, Solder pin length (l): 3.2 mm, tinned, Black, Box	4032248230846 50 pc(s).	IEC: 320 V / 17.5 A UL: 300 V / 10 A	Box
-----------------------------------	----------------------------	---	-------------------------	---	-----

**SC 3.81/90F**


The SC pin header has a parallel (recumbent) plugging direction in relation to the PCB. It is available in closed (G) and screw flange (F) versions. Weidmüller's 3.81-mm-pitch (0.15 inch) plug-in connectors are compatible with the layouts of standard connectors. They support a flood-light display and offer space for labelling and coding.

- 320 V (IEC) / 300 V (UL)
- 17.5 A (IEC) / 10 A (UL)

**General ordering data**

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SC 3.81/04/90F 3.2SN GN BX	<a href="#">1793440000</a>	PCB plug-in connector, male header, Flange, Solder connection, 3.81 mm, No. of poles: 4, 90°, Solder pin length (l): 3.2 mm, tinned, Pale green, Box	4032248228713 50 pc(s).		IEC: 320 V / 17.5 A UL: 300 V / 10 A	Box
SC 3.81/04/90F 3.2SN OR BX	<a href="#">1942470000</a>	PCB plug-in connector, male header, Flange, Solder connection, 3.81 mm, No. of poles: 4, 90°, Solder pin length (l): 3.2 mm, tinned, Orange, Box	4032248655120 50 pc(s).		IEC: 320 V / 17.5 A UL: 300 V / 10 A	Box
SC 3.81/04/90F 3.2SN BK BX	<a href="#">1793350000</a>	PCB plug-in connector, male header, Flange, Solder connection, 3.81 mm, No. of poles: 4, 90°, Solder pin length (l): 3.2 mm, tinned, Black, Box	4032248228423 50 pc(s).		IEC: 320 V / 17.5 A UL: 300 V / 10 A	Box

**OMNIMATE Signal - series BC/SC 3.81  
BCZ 3.81/04/90F SN BK BX**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Mating connector (conditionally pluggable)**
**SC-SMT 3.81/180G Box**


High-temperature-resistant pin header (SC-SMT 180G) in 3.81-mm pitch (0.15 inch)

- Plugging direction is perpendicular to PCB (standing)
- Closed (G) .
- Packed either in box (BX) or on anti-static roll (tape-on-reel, RL)
- Pin length of either 1.5 mm or 3.2 mm

Weidmüller's 3.81-mm-pitch (0.15 inch) plug-in connectors are compatible with the layouts of standard connectors and offer space for labelling and coding.

- 320 V (IEC) / 300 V (UL)
- 14.9 A (IEC) / 10 A (UL)

**General ordering data**

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SC-SMT 3.81/04/180G 1.5SN BK BX	<a href="#">1863750000</a>	PCB plug-in connector, male header, closed side, Reflow solder connection, 3.81 mm, No. of poles: 4, 180°, Solder pin length (l): 1.5 mm, tinned, Black, Box	4032248428915	50 pc(s).	IEC: 320 V / 17.5 A UL: 300 V / 10 A	Box
SC-SMT 3.81/04/180G 3.2SN BK BX	<a href="#">1862950000</a>	PCB plug-in connector, male header, closed side, Reflow solder connection, 3.81 mm, No. of poles: 4, 180°, Solder pin length (l): 3.2 mm, tinned, Black, Box	4032248428137	50 pc(s).	IEC: 320 V / 17.5 A UL: 300 V / 10 A	Box

**SC 3.81/90G**


The SC pin header has a parallel (recumbent) plugging direction in relation to the PCB. It is available in closed (G) and screw flange (F) versions.

Weidmüller's 3.81-mm-pitch (0.15 inch) plug-in connectors are compatible with the layouts of standard connectors. They support a flood-light display and offer space for labelling and coding.

- 320 V (IEC) / 300 V (UL)
- 17.5 A (IEC) / 10 A (UL)

**General ordering data**

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SC 3.81/04/90G 3.2SN OR BX	<a href="#">1942070000</a>	PCB plug-in connector, male header, closed side, Solder connection, 3.81 mm, No. of poles: 4, 90°, Solder pin length (l): 3.2 mm, tinned, Orange, Box	4032248655502	50 pc(s).	IEC: 320 V / 17.5 A UL: 300 V / 10 A	Box
SC 3.81/04/90G 3.2SN BK BX	<a href="#">1793150000</a>	PCB plug-in connector, male header, closed side, Solder connection, 3.81 mm, No.	4032248227648	50 pc(s).	IEC: 320 V / 17.5 A UL: 300 V / 10 A	Box

## OMNIMATE Signal - series BC/SC 3.81 BCZ 3.81/04/90F SN BK BX

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

### Mating connector (conditionally pluggable)

of poles: 4, 90°, Solder pin  
length (l): 3.2 mm, tinned,  
Black, Box

SC	<a href="#">1793260000</a>	PCB plug-in connector, male	4032248227730 50 pc(s).	IEC: 320 V / 17.5 A	Box
3.81/04/90G		header, closed side, Solder		UL: 300 V / 10 A	
3.2SN GN BX		connection, 3.81 mm, No.			
		of poles: 4, 90°, Solder pin			
		length (l): 3.2 mm, tinned,			
		Pale green, Box			

### SC 3.81/180G



The SC pin header has a perpendicular (standing) plugging direction in relation to the PCB. It is available in closed (G) and screw flange (F) versions. Weidmüller's 3.81-mm-pitch (0.15 inch) plug-in connectors are compatible with the layouts of standard connectors and offer space for labelling and coding.

- 320 V (IEC) / 300 V (UL)
- 17.5 A (IEC) / 10 A (UL)

### General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SC	<a href="#">1793630000</a>	PCB plug-in connector, male	4032248230754 50 pc(s).		IEC: 320 V / 17.5 A	Box
3.81/04/180G		header, closed side, Solder			UL: 300 V / 10 A	
3.2SN GN BX		connection, 3.81 mm, No.				
		of poles: 4, 180°, Solder pin				
		length (l): 3.2 mm, tinned,				
		Pale green, Box				
SC	<a href="#">1942860000</a>	PCB plug-in connector, male	4032248654734 50 pc(s).		IEC: 320 V / 17.5 A	Box
3.81/04/180G		header, closed side, Solder			UL: 300 V / 10 A	
3.2SN OR BX		connection, 3.81 mm, No.				
		of poles: 4, 180°, Solder pin				
		length (l): 3.2 mm, tinned,				
		Orange, Box				
SC	<a href="#">1793540000</a>	PCB plug-in connector, male	4032248230457 50 pc(s).		IEC: 320 V / 17.5 A	Box
3.81/04/180G		header, closed side, Solder			UL: 300 V / 10 A	
3.2SN BK BX		connection, 3.81 mm, No.				
		of poles: 4, 180°, Solder pin				
		length (l): 3.2 mm, tinned,				
		Black, Box				

**OMNIMATE Signal - series BC/SC 3.81  
BCZ 3.81/04/90F SN BK BX**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Mating connector (conditionally pluggable)**
**SC-SMT 3.81/90G Tape**


High-temperature-resistant pin header (SC-SMT 90G) in 3.81-mm pitch (0.15 inch)

- Plugging direction parallel to PCB (recumbent)
- Closed (G)
- Packed either in box (BX) or on anti-static roll (tape-on-reel, RL)
- Pin length of either 1.5 mm or 3.2 mm

Weidmüller's 3.81-mm-pitch (0.15 inch) plug-in connectors are compatible with the layouts of standard connectors and offer space for labelling and coding.

- 320 V (IEC) / 300 V (UL)
- 14.9 A (IEC) / 10 A (UL)

**General ordering data**

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SC-SMT 3.81/04/90G 1.5SN BK RL	<a href="#">1863160000</a>	PCB plug-in connector, male header, closed side, Reflow solder connection, 3.81 mm, No. of poles: 4, 90°, Solder pin length (l): 1.5 mm, tinned, Black, Tape	4032248428359	400 pc(s).	IEC: 320 V / 17.5 A UL: 300 V / 10 A	Tape
SC-SMT 3.81/04/90G 3.2SN BK RL	<a href="#">1862860000</a>	PCB plug-in connector, male header, closed side, Reflow solder connection, 3.81 mm, No. of poles: 4, 90°, Solder pin length (l): 3.2 mm, tinned, Black, Tape	4032248427796	400 pc(s).	IEC: 320 V / 17.5 A UL: 300 V / 10 A	Tape

**SC-SMT 3.81/180G Tape**


High-temperature-resistant pin header (SC-SMT 180G) in 3.81-mm pitch (0.15 inch)

- Plugging direction is perpendicular to PCB (standing)
- Closed (G)
- Packed either in box (BX) or on anti-static roll (tape-on-reel, RL)
- Pin length of either 1.5 mm or 3.2 mm

Weidmüller's 3.81-mm-pitch (0.15 inch) plug-in connectors are compatible with the layouts of standard connectors and offer space for labelling and coding.

- 320 V (IEC) / 300 V (UL)
- 14.9 A (IEC) / 10 A (UL)

**General ordering data**


Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SC-SMT 3.81/04/180G 1.5SN BK RL	<a href="#">1864290000</a>	PCB plug-in connector, male header, closed side, Reflow solder connection, 3.81 mm, No. of poles: 4, 180°	4032248429363	300 pc(s).	IEC: 320 V / 17.5 A UL: 300 V / 10 A	Tape

**OMNIMATE Signal - series BC/SC 3.81  
BCZ 3.81/04/90F SN BK BX**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Mating connector (conditionally pluggable)**

SC-SMT 3.81/04/180G 3.2SN BK RL	<a href="#">1863490000</a>	Solder pin length (l): 1.5 mm, tinned, Black, Tape	PCB plug-in connector, male header, closed side, Reflow solder connection, 3.81 mm, No. of poles: 4, 180°, Solder pin length (l): 3.2 mm, tinned, Black, Tape	4032248428571 300 pc(s). IEC: 320 V / 17.5 A UL: 300 V / 10 A	Tape
---------------------------------------	----------------------------	---	--	---	------

**SC-SMT 3.81/90G Box**


High-temperature-resistant pin header (SC-SMT 90G) in 3.81-mm pitch (0.15 inch)

- Plugging direction parallel to PCB (recumbent)
- Closed (G)
- Packed either in box (BX) or on anti-static roll (tape-on-reel, RL)
- Pin length of either 1.5 mm or 3.2 mm

Weidmüller's 3.81-mm-pitch (0.15 inch) plug-in connectors are compatible with the layouts of standard connectors and offer space for labelling and coding.

- 320 V (IEC) / 300 V (UL)
- 14.9 A (IEC) / 10 A (UL)

**General ordering data**

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
SC-SMT 3.81/04/90G 1.5SN BK BX	<a href="#">1862980000</a>	PCB plug-in connector, male header, closed side, Reflow solder connection, 3.81 mm, No. of poles: 4, 90°, Solder pin length (l): 1.5 mm, tinned, Black, Box	4032248428083	50 pc(s).	IEC: 320 V / 17.5 A UL: 300 V / 10 A	Box
SC-SMT 3.81/04/90G 3.2SN BK BX	<a href="#">1862490000</a>	PCB plug-in connector, male header, closed side, Reflow solder connection, 3.81 mm, No. of poles: 4, 90°, Solder pin length (l): 3.2 mm, tinned, Black, Box	4032248427628	50 pc(s).	IEC: 320 V / 17.5 A UL: 300 V / 10 A	Box

