

**HDC kits
HDC-KIT-HA 10.110**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



HDC kits are standardized kits for assembling complete plug-in connectors.
 The HDC kits normally consist of a male insert, a female insert, a plug housing, a bulkhead housing and a cable gland.
 Weidmüller offers a range of standard connector combinations with metric or PG cable entry threads.
 The wire connection level is designed as a screw element. All screw connections are equipped with a wire protection spring.
 Screw connection

General ordering data

Type	HDC-KIT-HA 10.110
Order No.	1884310000
Version	RockStar® HDC kits-Heavy-duty connectors, Kit, HA, Size: 2, Poles: 10, Screw connection, 250 V, 16 A, PG 16
GTIN (EAN)	4032248488599
Qty.	1 pc(s).

Data sheet

**HDC kits
HDC-KIT-HA 10.110**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Net weight 350 g

Temperatures

Limit temperature -40 °C ... 100 °C

Environmental Product Compliance

REACH SVHC Lead 7439-92-1,
Potassium perfluorobutane
sulfonate 29420-49-3

General data

Cable glands	PG 16	Connection type PE	Screw connection
Material	diecast aluminium	Number of poles	10
Rated current (DIN EN 61984)	16 A	Rated voltage (DIN EN 61984)	250 V
Series	HA	Size	2

Version

Conductor cross-section, max.	2.5 mm ²	Conductor cross-section, min.	0.5 mm ²
Material	diecast aluminium	Max. torque for main contact	0.55 Nm
Min. torque for main contact	0.5 Nm	Size	2
Surface finish	Powder coating	Type of connection	Screw connection

Classifications

ETIM 6.0	EC002943	ETIM 7.0	EC002943
eClass 9.0	27-44-02-92	eClass 9.1	27-44-01-90
eClass 10.0	27-44-02-92	UNSPSC	30-21-18-01

Approvals

Approvals



ROHS Conform

Downloads

Brochure/Catalogue	FL FIELDWIRING EN
Engineering Data	EPLAN, WSCAD
Engineering Data	STEP