

**VG K (standard plastic cable gland)
VG M32-K67**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Cable glands for professional use in industrial applications which meet the highest demands in terms of quality and safety. They are available made from polyamide, polystyrene and brass.

General ordering data

Type	VG M32-K67
Order No.	1909720000
Version	VG K (standard plastic cable gland), Cable glands, M 32, 15 mm, OD min. 18 - OD max. 25 mm, Polyamide 6
GTIN (EAN)	4032248536641
Qty.	20 pc(s).

Creation date April 13, 2020 5:24:32 PM CEST

**VG K (standard plastic cable gland)
VG M32-K67**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

Length	56 mm	Length (inches)	2.205 inch
Net weight	37.5 g		

General information

Material	Polyamide 6	Cable glands	metric
External thread	M 32	Pitch of thread	1.5 mm
Length of thread	15 mm	AF size 1	42 mm
Protection degree	IP67	Operating temperature range, min.	-20 °C
Operating temperature range, max.	100 °C	Outer cable diameter, min.	18 mm
Outer cable diameter, max.	25 mm	UL 94 flammability rating	V-2
Seal insert	NBR	Tightening torque	5 Nm
Torque for cap nut, min.	12 Nm	Torque for cap nut, max.	13 Nm
Torque for connecting adapter, min.	7.5 Nm	Torque for connecting adapter, max.	8.5 Nm
Torque for lock nut, min.	7.5 Nm	Torque for lock nut, max.	8.5 Nm
Standards	EN/IEC 62444		

Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
eClass 9.0	27-14-44-32	eClass 9.1	27-14-44-32
eClass 10.0	27-14-44-32	UNSPSC	30-21-18-01

Approvals

Approvals



ROHS Conform

Downloads

Brochure/Catalogue	CAT 3 HDC 17/18 EN CAT 5 ENCL 17/18 EN
Engineering Data	EPLAN, WSCAD
Engineering Data	STEP