

IE-S1DS2VE0030T01T01-E**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Single pair Ethernet is a technology that only requires one pair of wires to transmit data and power. The resulting benefits will make SPE the preferred network at the field level and beyond.

Advantages of Single Pair Ethernet

- **Consistent:** Single Pair Ethernet enables uniform Ethernet-based communication from the sensor to the cloud
- **Future-proof:** key technology for Industry 4.0 and IIoT
- **Flexible:** ranges of up to 1000 m and transmission properties of up to 1 Gbps enable use across applications
- **Innovative:** lighter, less space required, and reduced installation effort

General ordering data

Version	Patch cable, SPE plug (IEC 63171-2) - IP20 socket contact straight, SPE plug (IEC 63171-2) - IP20 socket contact straight, T1-B, PVC, 3 m
Order No.	2725850030
Type	IE-S1DS2VE0030T01T01-E
GTIN (EAN)	4050118825329
Qty.	1 pc(s).

IE-S1DS2VE0030T01T01-E
Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data
Dimensions and weights

Length	3 m	Length (inches)	118.11 inch
Net weight	0.109 g		

Temperatures

Operating temperature	-40 °C...80 °C
-----------------------	----------------

Electrical properties

Dielectric strength, contact / contact	1000 V DC	Dielectric strength, contact / shield	2250 V DC
PoE / PoE+	PoDL acc. to IEEE 802.3bu / cg		

Standards

Connector standard	IEC 63171-2
--------------------	-------------

Cable structure

Colour coding	white / blue	Complete shielding	Shielding braid made from copper wiring
Cross-section	2*AWG 22	Insulation	PE
Insulation diameter 2	1.65 mm	Material sheath	PVC
Number of wires	2	Overlap of shielding braid	80 %
Sheath diameter, max.	5.3 mm	Sheath diameter, min.	4.9 mm
Sheathing colour	black	Shielding	STP
Strands	7		

Electrical properties of cable

Capacity at 800 Hz	1.6 nF/km	Category	T1-B
Characteristic impedance	100 ± 15 Ω at 20 MHz	Coupling attenuation 1 to 600 MHz	Type I
Rated current	3.5 A	Rated voltage (DC)	60 V
Resistance differential	2 %	Test voltage: wire-wire-shield	1 kV DC, 1 min
Transmission rate	10/100 MBit/s, 1000 MBit/s		

Mechanical and material properties of cable

Bending radius	20 mm	Colour	black
Halogen	Yes	Resistance to oils	IRM 902/903 oil resistance test at (70°Cx4h)
Resistance to spread of flame	FT1	UV-resistant	Complies with UL 1581 Sec. 1200

IE-S1DS2VE0030T01T01-E

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Plug

Plug	Cable side	left
	Version of contact face	SPE
	Protection degree (IP)	IP20
	Gender of contact	female contact
	Outlet direction	straight
	Version of connector	plug
	Housing main material	Plastic
	According to Standard	IEC 63171-2
	Status indicator available	No
	Shielding available	Yes
	Cable side	right
	Version of contact face	SPE
	Protection degree (IP)	IP20
	Gender of contact	female contact
	Outlet direction	straight
	Version of connector	plug
	Housing main material	Plastic
	According to Standard	IEC 63171-2
	Status indicator available	No
	Shielding available	Yes
Plug left	SPE, IP20, female contact, straight, plug, Plastic, IEC 63171-2, shielded	
Plug right	SPE, IP20, female contact, straight, plug, Plastic, IEC 63171-2, shielded	

Plug, left

Connector left	SPE plug (IEC 63171-2) - IP20 socket contact straight	Plug left	SPE, IP20, female contact, straight, plug, Plastic, IEC 63171-2, shielded
----------------	---	-----------	---

Plug, right

Connector right	SPE plug (IEC 63171-2) - IP20 socket contact straight	Housing main material	Elastollan
Plug right	SPE, IP20, female contact, straight, plug, Plastic, IEC 63171-2, shielded		

Classifications

ETIM 6.0	EC002599	ETIM 7.0	EC002599
ETIM 8.0	EC002599	ETIM 9.0	EC002599
ECLASS 9.0	27-06-03-08	ECLASS 9.1	27-06-03-08
ECLASS 10.0	27-06-03-08	ECLASS 11.0	27-06-03-08
ECLASS 12.0	27-06-03-08	ECLASS 13.0	27060308

Approvals

Approvals



UL File Number Search	UL Website
Certificate no. (cULus)	E316369

Creation date December 5, 2023 9:55:50 AM CET

Catalogue status 24.11.2023 / We reserve the right to make technical changes.

3

Data sheet

IE-S1DS2VE0030T01T01-E

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format

Data sheet

IE-S1DS2VE0030T01T01-E

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Detailed drawing



Dimensional drawing

