

## POK MOPL 1222

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

### Similar to illustration



The Klippon® POK enclosure range is made from a high-quality glass fibre reinforced polyester and is ideal for applications and environments where corrosion resistance, impact resistance and a high IP protection class are a requirement.

Key features of the extensive product range:

- Available in 17 sizes
- Two standard finishes (colours): grey (similar to RAL 7001 for industrial use) and black (similar to RAL 9011 for harsh environments, Ex)
- Cover with stainless steel screws in cross-head / slotted design
- Moulded gasket made of silicone or chloroprene
- Fixing holes outside the sealed area to ensure high ingress protection of IP66
- Impact resistance up to 7 Joules
- Mounting directly in the enclosure or using an internal mounting plate
- Direct wall mounting possible using fixing holes or mounting feet
- Fastening thread to attach mounting rails and plates
- Up to E60 fire rating dependent on the configuration
- Weidmüller can manufacture and supply this enclosure to match customer specifications - fitted with all necessary terminals and cable glands.

### General ordering data

Version	Klippon POK (polyester empty enclosure), Mounting plate, Height: 107 mm, Width: 207 mm, Depth: 1.5 mm, Material: Sheet steel, galvanized, Miscellaneous, silver
Order No.	<a href="#">951060000</a>
Type	POK MOPL 1222
GTIN (EAN)	4008190498238
Qty.	1 pc(s).

## POK MOPL 1222

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	1.5 mm	Depth (inches)	0.059 inch
Height	107 mm	Height (inches)	4.213 inch
Width	207 mm	Width (inches)	8.15 inch
Mounting dimension - height	52 mm	Mounting dimension - width	193 mm
Net weight	237 g		

## Certificate numbers enclosure

Certificate No. (EAC) RUC-DE.BE02.B.00173

## General information

Material	Sheet steel, galvanized	Material thickness	1.5 mm
Surface finish	Miscellaneous	Type of fixing	when screwed in

## Classifications

ETIM 6.0	EC000213	ETIM 7.0	EC000213
ETIM 8.0	EC000213	ECLASS 9.0	27-40-06-39
ECLASS 9.1	27-18-92-90	ECLASS 10.0	27-40-06-39
ECLASS 11.0	27-40-06-39	ECLASS 12.0	27-40-06-39

## Approvals

Approvals



ROHS Conform

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	