


VT COMBI PRO**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The main function of the voltage tester is to establish if voltage is present. A 2-pole voltage tester is the only approved testing instrument that fulfils the requirements of work protection regulations.

- with LED-Display
- acc. to VDE standard
- high peak voltage strength
- the right tester for every application

General ordering data

Version	Testing tools, 2-pole voltage tester type 1156
Order No.	9918860000
Type	VT COMBI PRO
GTIN (EAN)	4032248405749
Qty.	1 pc(s).

VT COMBI PRO

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	67 mm	Depth (inches)	2.638 inch
Height	33 mm	Height (inches)	1.299 inch
Width	264 mm	Width (inches)	10.394 inch
Weight	290 g	Net weight	356 g

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Technical data

Description of article	Voltage tester up to 690 V / 100 Hz LED
------------------------	---

Measuring and testing devices

AC voltage display	6, 12, 24, 50, 120, 230, 400, 690 V	AC voltage measuring range	6-690 V
Battery type	1.5 V type AAA battery	Buzzer	Yes
Continuity test	Yes - visual + acoustic	DC voltage display	6, 12, 24, 50, 120, 230, 400, 690 V
DC voltage measuring range	690 V	Display	LED
Frequency range, max.	400 Hz	Frequency range, min.	16 Hz
Insulation test	8 kV	Load switchable	Yes
Measuring range category	CAT III – 690V/CAT IV – 600V	Note	Screw-on, thicker test probes
One-handed operation	Yes	Peak voltage resistance	8 kV
Phase sequence display	Yes	Protection degree	IP65
RCD circuit breaker	The selectable load enables conscious triggering of a 30 mA RCD circuit breaker	Rated voltage, max.	690 V AC/DC
Rated voltage, min.	6 V	Residual-current test	Yes
Test probe illumination	Yes	Test probe protection GS 38	Yes
Tested and approved according to	IEC 61243-3:2014 (DIN EN 61243-3:2015-08)	Working temperature, max.	55 °C
Working temperature, min.	-15 °C		

Classifications

ETIM 6.0	EC000494	ETIM 7.0	EC000494
ETIM 8.0	EC000494	ECLASS 9.0	27-20-03-08
ECLASS 9.1	27-20-03-08	ECLASS 10.0	27-20-03-08
ECLASS 11.0	27-20-03-08		

Approvals

Approvals



ROHS	Conform
------	---------

VT COMBI PRO

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Approval/Certificate/Document of Conformity	9918860000_DECLARATION_OF_CONFORMITY.pdf
Product Change Notification	PCN-PW641110-20180410-00-A EN PCN-PW641110-20180410-00-A DE
User Documentation	BANL_manual 2pol Tester
Catalogues	Catalogues in PDF-format
Brochures	