

SAIE-M12S-5-1.0V-HW-PG9

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Various build-in connectors are required for the connections on the device side of the sensor/actuator cabling. These are available in the versions M12, M8 and M5.

General ordering data

Version	Built-in plugs, pin, straight, Mounting thread: PG 9, Number of poles: 5, Strand / cable length: 1 m, Rear panel mounting
Order No.	1115630000
Type	SAIE-M12S-5-1.0V-HW-PG9
GTIN (EAN)	4032248895687
Qty.	10 items

SAIE-M12S-5-1.0V-HW-PG9

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Net weight 40 g

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Technical specifications for cable

Cable length	1 m	Core cross-section	0.34 mm ²
Strand / cable length	1 m	Sheath material	PVC
Colour coding	brown, white, blue, black, Green/yellow	Number of poles	5

Technical data customisable plug-in connectors

Number of poles	5	Coding	A-coded
Contact surface	Ni/Au	Type of connection	Pin connector
Housing main material	Zinc diecast	Insulation resistance	109 Ω
Contact material	CuZn	Nominal voltage	60 V
Nominal current	4 A	Protection degree	IP67, when screwed in
Pollution severity	3	Temperature range of housing	-25...+80 °C

Standards

Connector standard IEC 61076-2-101


General data

Number of poles	5	Cable length	1 m
Coding	A-coded	Contact surface	Ni/Au
Core cross-section	0.34 mm ²	Type of connection	Pin connector
Housing main material	Zinc diecast	Insulation resistance	109 Ω
Contact material	CuZn	Type of mounting	Rear panel mounting
Nominal voltage	60 V	Nominal current	4 A
AF size	19 mm	Protection degree	IP67, when screwed in
Pollution severity	3	Connection 1	M12
Connection 2	Flying wires	Strand / cable length	1 m
Sheath material	PVC	Mounting thread	PG 9
Temperature range of housing	-25...+80 °C	Conductor O.D.	-


Classifications

ETIM 6.0	EC002635	ETIM 7.0	EC003570
ETIM 8.0	EC003570	ETIM 9.0	EC003570
ETIM 10.0	EC003570	ECLASS 9.0	27-44-01-03
ECLASS 9.1	27-44-01-03	ECLASS 10.0	27-44-01-03
ECLASS 11.0	27-44-01-03	ECLASS 12.0	27-44-01-03
ECLASS 13.0	27-44-01-03	ECLASS 14.0	27-44-01-03
ECLASS 15.0	27-44-01-03		


Wiring diagram




Pole scheme



Dimensioned drawing



Dimensioned drawing



Detailed drawing

