

HSS 1.0-3.2 EL W30M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

General ordering data

| | |
|------------|--|
| Version | Conductor and cable markers, 1 - 3.2 mm, white |
| Order No. | 1505850000 |
| Type | HSS 1.0-3.2 EL W30M |
| GTIN (EAN) | 4050118314236 |
| Qty. | 1 items |

HSS 1.0-3.2 EL W30M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform
 UL File Number Search [UL Website](#)
 Certificate No. (cURus) E366310

Dimensions and weights

| | | | |
|------------|----------|-----------------|-------------|
| Depth | 0.77 mm | Depth (inches) | 0.0303 inch |
| Width | 5.6 mm | Width (inches) | 0.2205 inch |
| Length | 30000 mm | Length (inches) | 1181.1 inch |
| Net weight | 172 g | | |

Temperatures

Operating temperature range -55...135 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

| | | | |
|-----------------------------------|--|-----------------------------------|---|
| Type of printing | neutral | Width | 5.6 mm |
| Operating temperature range, max. | 135 °C | Operating temperature range, min. | -55 °C |
| Colour | white | Halogen | Yes |
| Length | 30000 mm | Basic material | Polyolefine |
| Printed characters | without | Recommended industries | Plant manufacture, Energy, Device manufacturer, Machinery |
| compatible printer | THM MULTIMARK , THM MULTIMARK PLUS | Operating temperature range | -55...135 °C |

Conductor and cable markers

| | | | |
|-----------------------------------|---------------------------|-------------------------------|---------------------|
| Halogen | Yes | Conductor cross-section, max. | 1.5 mm ² |
| Conductor cross-section, min. | 0.5 mm ² | Conductor O.D., max. | 3.2 mm |
| Conductor O.D., min. | 1 mm | Rate of shrinkage | 3:1 |
| Recommended shrinking temperature | 90 °C | Text field width | 0 mm |
| Text field height | 5.4 mm | Conductor O.D. | 1 - 3.2 mm |
| Cross-section for connected wire | 0.5 - 1.5 mm ² | | |

Important note

Product information External roll holder 1302920000 necessary

Classifications

| | | | |
|------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001530 | ETIM 7.0 | EC001530 |
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ETIM 10.0 | EC001530 | ECLASS 9.0 | 27-40-04-01 |
| ECLASS 9.1 | 27-40-04-01 | ECLASS 10.0 | 27-40-04-01 |

HSS 1.0-3.2 EL W30M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

| | | | |
|-------------|-------------|-------------|-------------|
| ECLASS 11.0 | 27-28-11-02 | ECLASS 12.0 | 27-28-11-02 |
| ECLASS 13.0 | 27-28-11-02 | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 | | |

HSS 1.0-3.2 EL W30M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

