


SAIE-M12S-8-0.5U-M16**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Various build-in connectors are required for the connections on the device side of the sensor/actuator cabling. These are available in the versions M12, M8 and M5.

General ordering data

Version	Built-in plugs, M12, pin, straight, Mounting thread: M 16 x 1.5, Number of poles: 8, Strand / cable length: 0.5 m, Front mounting
Order No.	1861110000
Type	SAIE-M12S-8-0.5U-M16
GTIN (EAN)	4032248419159
Qty.	1 items

SAIE-M12S-8-0.5U-M16

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E307231

Dimensions and weights

Net weight	29 g
------------	------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	ebf89fc8-a87f-4691-b87a-dfb9921774b4

Technical specifications for cable

PE function	No	Core cross-section	0.25 mm ²
Wire cross section (Print/Online)	0.34 (4- and 5-pole)/ 0.25 (8-pole)/ 0.14 (12-pole)	Strand / cable length	0.5 m
Colour coding	white, brown, green, yellow, grey, pink, blue, red	Number of poles	8

Technical data customisable plug-in connectors

Number of poles	8	Coding	A-coded
Contact surface	Gold-plated	Housing main material	Brass, nickel-plated
Nominal voltage	30 V	Nominal current	2 A
Protection degree	IP67, when screwed in	Plugging cycles	≥ 100
Rated current	4 A (4- and 5-pole)/ 2 A (8-pole)/ 1.5 A (12-pole)	Temperature range of housing	-30...+90 °C

Standards

Connector standard	IEC 61076-2-101
--------------------	-----------------

General data

Number of poles	8
Coding	A-coded
Connection thread	M12
Contact surface	Gold-plated
Tightening torque	1 Nm
Core cross-section	0.25 mm ²
Housing main material	Brass, nickel-plated
Type of mounting	Front mounting
Nominal voltage	30 V
Nominal current	2 A
Protection degree	IP67, when screwed in
Plugging cycles	≥ 100
Basic material	PUR

SAIE-M12S-8-0.5U-M16

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Rated voltage	250 V (4-pole)/ 60 V (5-pole)/ 30 V (8 and 12-pole)	
Rated current	4 A (4- and 5-pole)/ 2 A (8-pole)/ 1.5 A (12-pole)	
Wire cross section (Print/Online)	0.34 (4- and 5-pole)/ 0.25 (8-pole)/ 0.14 (12-pole)	
Connection 1	M12	
Connection 2	Flying wires	
Strand / cable length	0.5 m	
Mounting thread	M 16 x 1.5	
Mounting torque range	2 Nm	
Mounting torque	max.	2 Nm
Temperature range of housing	-30...+90 °C	
Conductor O.D.	-	

Classifications

ETIM 6.0	EC002635	ETIM 7.0	EC003570
ETIM 8.0	EC003570	ETIM 9.0	EC003570
ETIM 10.0	EC003570	ECLASS 9.0	27-44-01-03
ECLASS 9.1	27-44-01-03	ECLASS 10.0	27-44-01-03
ECLASS 11.0	27-44-01-03	ECLASS 12.0	27-44-01-03
ECLASS 13.0	27-44-01-03	ECLASS 14.0	27-44-01-03
ECLASS 15.0	27-44-01-03		

Pole scheme

