

IE-C6ES8UG0013A20XXX-E**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**General ordering data**

Version	System cable, RJ45 IP 20, Open, Cat.6A / Class EA (ISO/IEC 11801 2010), PUR, 1.3 m
Order No.	2439100013
Type	IE-C6ES8UG0013A20XXX-E
GTIN (EAN)	4050118451733
Qty.	1 pc(s).

IE-C6ES8UG0013A20XXX-E

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Length	1.3 m	Length (inches)	51.181 inch
Net weight	81.65 g		

Temperatures

Storage temperature	-40 °C...80 °C	Operating temperature	-40 °C...80 °C
Installation temperature	-15 °C...60 °C		

Cable specific standards

Corrosiveness of fumes	to IEC 60754-2	Generic communication cable facilities	EN 50173-1:2007, ISO / IEC 11801:2002
Standard, assembly	UL-Style 20963 (80°C/30V)		

Cable structure

Arrangement of wire cores	Twisted pair	Colour sequence or wires - wire pairs	white - blue, white - orange, white - green, white - brown
Complete shielding	Shielding braid made from copper wiring	Cross-section	4*2*AWG 26/7 - 4*2*0.128 mm ²
Insulation	PE	Insulation cross-section	1.03 mm
Material sheath	PUR	Sheath diameter, max.	6.5 mm
Sheath diameter, min.	6.1 mm	Sheathing colour	green (RAL 6018)
Shielding	S/FTP	Shielding braid thickness	0.1 mm
Standard designations	S/FTP, LIO2YSC11Y 4x2x0.15 PIMF FRNC GN	Strands	7
Wire material	Stranded tin-plated copper wire	Wire pair shielding	Aluminium foil

Electrical properties of cable

Capacity at 1 kHz	45 nF/km	Category	Cat.6A / Class EA (ISO/ IEC 11801 2010)
Characteristic impedance	100 ± 5 Ω at 100MHz	Delay skew	3 ns/100m
Loop resistance	290 Ω/km	Signal propagation time	4.5 ns/m
Test voltage: wire-wire-shield	700 V AC	Transfer impedance	15 mΩ/m at 1 MHz, 10 mΩ/m at 10 MHz, 30 mΩ/m at 30 MHz

Mechanical and material properties of cable

Abrasion resistance	very good	Corrosiveness of fumes	to IEC 60754-2
Halogen	halogen-free, according to IEC 60754-2	Min. bending radius, once only	5 x cable diameter
Min. bending radius, repetitive	10 x cable diameter	Pulling force	≤ 100 N
Resistance to oils	in accordance with IEC 60811-2-1	Resistance to spread of flame	in accordance with IEC 60332-1

IE-C6ES8UG0013A20XXX-E

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Plug

Plug	Cable side	left
	Version of contact face	RJ45
	Protection degree (IP)	IP20
	Gender of contact	male contact
	Outlet direction	straight
	Housing main material	Zinc diecast
	Status indicator available	No
	Shielding available	Yes
	Cable side	right
	Version of cable end [In-Block]	free conductor end
Plug left	RJ45, IP20, male contact, straight, Zinc diecast, shielded	
Plug right	free conductor end	

Classifications

ETIM 6.0	EC002599	ETIM 7.0	EC002599
ETIM 8.0	EC002599	ETIM 9.0	EC002599
ECLASS 9.0	27-06-03-08	ECLASS 9.1	27-06-03-08
ECLASS 10.0	27-06-03-08	ECLASS 11.0	27-06-03-08
ECLASS 12.0	27-06-03-08	ECLASS 13.0	27060308

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN PI PROFINET CABLING EN