


AAP11 6/6X1.5 PE-LI**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

The unique modular concept can be tailored to every type of machine. The potential distribution terminal blocks AAP are successful thanks to their uniform design with two possible constructions – alternating or grouped. In the grouped structure of the control voltage distribution, the potentials are located on different terminal blocks and thus form entire potential blocks.

General ordering data

| | |
|------------|--|
| Version | Modular distribution terminals, PUSH IN, 6 mm ² , 500 V, 41 A, Green/yellow |
| Order No. | 2464740000 |
| Type | AAP11 6/6X1.5 PE-LI |
| GTIN (EAN) | 4050118479355 |
| Qty. | 20 items |

AAP11 6/6X1.5 PE-LI

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (cURus) E60693

Dimensions and weights

| | | | |
|--------------------------|-------------|----------------|-------------|
| Depth | 47 mm | Depth (inches) | 1.8504 inch |
| Depth including DIN rail | 48 mm | Height | 85.5 mm |
| Height (inches) | 3.3661 inch | Width | 8.1 mm |
| Width (inches) | 0.3189 inch | Net weight | 25.12 g |

Temperatures

| | | | |
|----------------------------------|----------------|----------------------------------|---------------|
| Storage temperature | -25 °C...55 °C | Ambient temperature | -5 °C...40 °C |
| Continuous operating temp., min. | -60 °C | Continuous operating temp., max. | 130 °C |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Material data

| | | | |
|--------------------------------|--------|---------------------------|--------------|
| Basic material | Wemid | Colour | Green/yellow |
| Colour of operational elements | orange | UL 94 flammability rating | V-0 |

Rating data IECEx/ATEX

| | | | |
|--------------------|---------------|---------------------|----------|
| Marking EN 60079-7 | Ex ec II C Gc | Ex 2014/34/EU label | II 2 G D |
|--------------------|---------------|---------------------|----------|

System specifications

| | | | |
|-------------------------------|-----|-------------------------------------|-------|
| End cover plate required | Yes | Number of potentials | 1 |
| Number of levels | 1 | Number of clamping points per level | 7 |
| Number of potentials per tier | 1 | Levels cross-connected internally | No |
| PE connection | Yes | Mounting rail | TS 35 |
| N-function | No | PE function | Yes |
| PEN function | No | | |

Additional technical data

| | | | |
|---------------------|-------|--------------------------|---------|
| Open sides | right | Type of fixing | Snap-on |
| Installation advice | Rail | Explosion-tested version | Yes |
| Type of mounting | TS 35 | | |

CSA rating data

| | | | |
|-------------------------------|--------|-----------------------|-----------------|
| Wire cross section max. (CSA) | 8 AWG | Certificate No. (CSA) | 200039-70089609 |
| Wire cross section min. (CSA) | 26 AWG | | |

AAP11 6/6X1.5 PE-LI

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Conductors for clamping (additional connection)

| | | | |
|---|----------------------|---|---------------------|
| Connection direction additional connection | top | Clamping range, further connection, max. | 1.5 mm ² |
| Clamping range, further connection, min. | 0.14 mm ² | Conductor cross-section, flexible plus plastic collar DIN 46228/1, further connection, max. | 1.5 mm ² |
| Conductor cross-section, flexible plus plastic collar DIN 46228/1, further connection, min. | 0.5 mm ² | Conductor cross-section, flexible, further connection, min. | 0.5 mm ² |
| Number of connections, additional connection | 6 | Rated cross-section, further connection | 1.5 mm ² |
| Blade size, additional connection | 0.4 x 2.0 mm | Cross-section for connected wire, multi-core, further connection, min. | 0.5 mm ² |
| Cross-section for connected wire, multi-core, further connection, max. | 1.5 mm ² | Rated current, additional connection | 17.5 A |
| Cross-section for connected wire, solid-core, further connection, min. | 0.5 mm ² | Cross-section for connected wire, solid-core, further connection, max. | 1.5 mm ² |
| Connection type, additional connection | PUSH IN | Cross-section for connected wire, flexible, further connection, max. | 1.5 mm ² |
| Stripping length , additional connection | 8 mm | | |

Conductors for clamping (rated connection)

| | |
|---|----------------------|
| Gauge to IEC 60947-1 | A5 |
| Wire connection cross section AWG, max. | AWG 8 |
| Connection direction | top |
| Stripping length | 12 mm |
| Type of connection | PUSH IN |
| Number of connections | 1 |
| Clamping range, max. | 6 mm ² |
| Clamping range, min. | 0.34 mm ² |
| Blade size | 1.0 x 5.5 mm |
| Wire connection cross section AWG, min. | AWG 22 |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 6 mm ² |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.34 mm ² |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 6 mm ² |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.34 mm ² |
| Wire connection cross section, finely stranded, max. | 6 mm ² |
| Wire connection cross section, finely stranded, min. | 0.34 mm ² |
| Connection cross-section, stranded, max. | 6 mm ² |
| Connection cross-section, stranded, min. | 0.34 mm ² |
| Twin wire-end ferrules, max. | 1.5 mm ² |
| Twin wire-end ferrules, min. | 0.5 mm ² |
| Wire connection cross-section, solid core, max. | 6 mm ² |
| Wire connection cross-section, solid core, min. | 0.34 mm ² |

AAP11 6/6X1.5 PE-LI

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

| | | | |
|---|--|---------|----------------------|
| Tube length for wire-end ferrule with plastic collar DIN 46228/4 | Tube length | min. | 10 mm |
| | | max. | 12 mm |
| | Cross-section for conductor connection | min. | 0.5 mm ² |
| | | max. | 1 mm ² |
| | Tube length | min. | 10 mm |
| | | max. | 18 mm |
| | Cross-section for conductor connection | nominal | 1.5 mm ² |
| | Tube length | min. | 12 mm |
| | max. | 18 mm | |
| Tube length for twin wire-end ferrule | Cross-section for conductor connection | nominal | 2.5 mm ² |
| | Tube length | min. | 10 mm |
| | | max. | 18 mm |
| | Cross-section for conductor connection | min. | 4 mm ² |
| | | max. | 6 mm ² |
| | Tube length | min. | 10 mm |
| | | max. | 12 mm |
| | Cross-section for conductor connection | nominal | 0.5 mm ² |
| Tube length for wire-end ferrule without plastic collar DIN 46228/1 | Tube length | min. | 10 mm |
| | | max. | 18 mm |
| | Cross-section for conductor connection | nominal | 0.75 mm ² |
| | Tube length | min. | 12 mm |
| | | max. | 18 mm |
| | Cross-section for conductor connection | min. | 1 mm ² |
| | | max. | 1.5 mm ² |
| | Tube length | min. | 10 mm |
| | max. | 18 mm | |
| | Cross-section for conductor connection | nominal | 4 mm ² |
| | Tube length | min. | 10 mm |
| | | max. | 18 mm |
| | Cross-section for conductor connection | min. | 6 mm ² |
| | | max. | 10 mm ² |

General

| | | | |
|---|--------|---------------------|---------------|
| Wire connection cross section AWG, max. | AWG 8 | Installation advice | Rail |
| Wire connection cross section AWG, min. | AWG 22 | Standards | IEC 60947-7-2 |
| Mounting rail | TS 35 | | |

Rating data

| | | | |
|-------------------------------------|-------------------|--|---------|
| Rated cross-section | 6 mm ² | Rated voltage | 500 V |
| Rated voltage to adjoining terminal | 500 V | Rated DC voltage | 500 V |
| Nominal current | 41 A | Current at maximum wires | 41 A |
| Standards | IEC 60947-7-2 | Volume resistance according to IEC 60947-7-x | 0.78 mΩ |
| Rated impulse withstand voltage | 6 kV | Power loss in accordance with IEC 60947-7-x | 1.31 W |
| Pollution severity | 3 | | |

AAP11 6/6X1.5 PE-LI

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

UL rating data

| | | | |
|--|--------|--|--------|
| Conductor size Factory wiring max. (cURus) | 8 AWG | Voltage size B (cURus) | 300 V |
| Voltage size D (cURus) | 300 V | Certificate No. (cURus) | E60693 |
| Conductor size Field wiring min. (cURus) | 26 AWG | Conductor size Factory wiring min. (cURus) | 26 AWG |
| Voltage size C (cURus) | 300 V | Conductor size Field wiring max. (cURus) | 8 AWG |

Important note

Product information The applicable safety regulations for the overload and short-circuit of the connected conductors must be followed. The total current of all connected conductors must not exceed the max. load current.

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000897 | ETIM 7.0 | EC000897 |
| ETIM 8.0 | EC000897 | ETIM 9.0 | EC000897 |
| ETIM 10.0 | EC000897 | ECLASS 9.0 | 27-14-11-20 |
| ECLASS 9.1 | 27-14-11-20 | ECLASS 10.0 | 27-14-11-20 |
| ECLASS 11.0 | 27-14-11-20 | ECLASS 12.0 | 27-14-11-20 |
| ECLASS 13.0 | 27-25-01-01 | ECLASS 14.0 | 27-25-01-01 |
| ECLASS 15.0 | 27-25-01-01 | | |

