

HDC MHP200 F 25**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Crimps provide a electrical and mechanical connection between wire and contact that is both secure and reliable. The optimal crimp connection is gas-tight and corrosion-resistant.

General ordering data

Version	Female, silver, 25 mm ²
Order No.	2514820000
Type	HDC MHP200 F 25
GTIN (EAN)	4050118528466
Qty.	10 pc(s).

HDC MHP200 F 25

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	20.8 g
------------	--------

Temperatures

Limit temperature	-40 °C ... 125 °C
-------------------	-------------------

General data

Conductor cross-section, max.	25 mm ²	Contact diameter, male Ø	9.5 mm
Cross-section for connected wire	25 mm ²	Material	Copper alloy
Production methods	turned	Stripping length, rated connection	19 mm
Surface finish	silver	Type	Female
Type of connection	Crimp connection	Version insert	MHP

Classifications

ETIM 6.0	EC000796	ETIM 7.0	EC000796
ETIM 8.0	EC000796	ETIM 9.0	EC000796
ECLASS 9.0	27-44-02-04	ECLASS 9.1	27-44-02-04
ECLASS 10.0	27-44-02-04	ECLASS 11.0	27-44-02-04
ECLASS 12.0	27-44-02-04	ECLASS 13.0	27-44-02-04
ECLASS 14.0	27-44-02-04		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	6eabd5ae-2d6b-409e-8bdf-87c27ee10e40

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format

HDC MHP200 F 25

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

