

QL 10 SAK6N**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030


32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Product image

Similar to illustration

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

General ordering data

Version	SAK Series, Cross-connector, for cross-connection link, Number of poles: 10
Order No.	0338300000
Type	QL 10 SAK6N
GTIN (EAN)	4008190176679
Qty.	20 pc(s).

QL 10 SAK6N

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	1 mm	Depth (inches)	0.039 inch
Height	6 mm	Height (inches)	0.236 inch
Width	77.1 mm	Width (inches)	3.035 inch
Net weight	3 g		

Temperatures

Storage temperature -25 °C...55 °C

Material data

Material Copper Colour grey

System specifications

Version for cross-connection link

Additional technical dataExplosion-tested version No Installation advice Direct mounting
Type of fixing when screwed in**Cross-connector**Number of cross-connected terminals 10 Rated current, 2-pole 57 A
Rated current, multi-pole 32 A Type Cross-connector**Dimensions**

Pitch in mm (P) 7.9 mm

General

Installation advice Direct mounting Number of poles 10

Rating data

Rated current 41 A

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ECLASS 9.0	27-14-11-40
ECLASS 9.1	27-14-11-40	ECLASS 10.0	27-14-11-40
ECLASS 11.0	27-14-11-40	ECLASS 12.0	27-14-11-40

Approvals

Approvals



ROHS Conform

Creation date June 7, 2023 9:29:15 AM CEST

Catalogue status 26.05.2023 / We reserve the right to make technical changes.

Data sheet**QL 10 SAK6N****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.comwww.weidmueller.com**Technical data****Downloads**Approval/Certificate/Document of
Conformity[EAC certificate](#)

Engineering Data

[CAD data – STEP](#)

Engineering Data

[WSCAD, Zuken E3.S](#)

User Documentation

[StorageConditionsTerminalBlocks](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures