

**WINDOW SET 160X120****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**General ordering data**

|            |                                                                                                              |
|------------|--------------------------------------------------------------------------------------------------------------|
| Version    | Klippon TB (Terminal Box), Window, Height: 160 mm, Width: 120 mm, Depth: 4 mm, Basic material: Polycarbonate |
| Order No.  | <a href="#">8000081760</a>                                                                                   |
| Type       | WINDOW SET 160X120                                                                                           |
| GTIN (EAN) | 4064675855859                                                                                                |
| Qty.       | 50 items                                                                                                     |

## WINDOW SET 160X120

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Depth      | 4 mm   | Depth (inches)  | 0.1575 inch |
| Height     | 160 mm | Height (inches) | 6.2992 inch |
| Width      | 120 mm | Width (inches)  | 4.7244 inch |
| Net weight | 2.8 g  |                 |             |

## Temperatures

|                       |                |
|-----------------------|----------------|
| Operating temperature | -35 °C...90 °C |
|-----------------------|----------------|

## Environmental Product Compliance

|                        |                       |
|------------------------|-----------------------|
| RoHS Compliance Status | Compliant             |
| REACH SVHC             | No SVHC above 0.1 wt% |

## General information

|                             |                 |                             |               |
|-----------------------------|-----------------|-----------------------------|---------------|
| Material thickness          | 4 mm            | Operating temperature, max. | 90 °C         |
| Operating temperature, min. | -35 °C          | UL 94 flammability rating   | V-0           |
| Standards                   | EN 45545-2:2020 | Impact resistance           | IK08          |
| Protection degree           | IP66            | Basic material              | Polycarbonate |

## General information on accessories

|                    |      |                |               |
|--------------------|------|----------------|---------------|
| Material thickness | 4 mm | Basic material | Polycarbonate |
|--------------------|------|----------------|---------------|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC002498    | ETIM 9.0    | EC002498    |
| ETIM 10.0   | EC002498    | ECLASS 14.0 | 27-37-13-92 |
| ECLASS 15.0 | 27-37-13-92 |             |             |