

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200730357](#)
Status: **Active**
Overview: Brad Micro-Change (M12) Connectors
Description: Micro-Change (1/2"-20 UNF) Double-Ended Cordset, 6 Poles, Male (Straight) to Female (Straight), 18 AWG, PVC Cable, 0.91m (3.0') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E152210

General

Product Family Industrial Cordsets
 Series [120073](#)
 Connector End A Micro-Change (1/2" - 20 UNF)
 Connector End B Micro-Change (1/2" - 20 UNF)
 IP Rating IP67
 Material - Contact Copper Alloy
 Overview [Brad Micro-Change \(M12\) Connectors](#)
 Product Name Micro-Change (1/2" - 20 UNF)
 Protocol PROFIBUS
 Region America
 Type Double Ended
 UPC 78678833310

Physical

Cable Diameter 6.22mm (.245")
 Cable Length 0.91m (3.0')
 Color - Cable Jacket Yellow
 Coupling Style Threaded
 Gender Female-Male
 Keyway Dual
 LED Indicator No
 Material - Cable Jacket PVC
 Material - Connector Body PVC
 Material - Coupling Nut Black Epoxy Coated Zinc
 Material - O-Ring Nitrile Rubber
 Material - Plating Mating Gold over Nickel
 Orientation Straight to Straight
 Poles 6
 Temperature Range - Operating -20°C to +105°C
 Wire Size AWG 22
 Wire/Cable Type UL 2661

Electrical

Current - Maximum per Contact 4.0A
 Voltage - Maximum 250V AC/DC

Material Info

Engineering Number 776030D02F030

Reference - Drawing Numbers

Sales Drawing SD-120073-001-001



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[120073 Series](#)

This document was generated on 01/08/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION