

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200980031](#)
Status: **Active**
Overview: Brad Micro-Change (M12) Connectors
Description: Micro-Change (M12) Double-Ended Cordset, 5 Poles, Female (90°) to Male (90°), 24 AWG, 2.0m (6.56') Length, PROFIBUS PUR Cable Preferred Version in Europe

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Cordsets
Series	120098
Connector End A	Micro-Change (M12)
Connector End B	Micro-Change (M12)
IP Rating	IP67
Material - Contact	Copper Alloy
Overview	Brad Micro-Change (M12) Connectors
Product Name	Micro-Change (M12)
Protocol	EtherNet
Region	America, Asia, Europe
Type	Double Ended
UPC	78678853594

Physical

Cable Diameter	8.00mm (.315")
Cable Length	2.0m (6.56')
Color - Cable Jacket	Purple
Coupling Style	Threaded
Gender	Female-Male
Keyway	Reverse
LED Indicator	No
Material - Cable Jacket	PUR
Material - Connector Body	PUR
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold over Nickel
Net Weight	190.215/g
Orientation	90° to 90°
Poles	5
Temperature Range - Operating	-20°C to +80°C
Wire Size AWG	24
Wire/Cable Type	Twisted Pair

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	60V AC/DC

Material Info

Engineering Number	BB5S33PP4M020
--------------------	---------------

Reference - Drawing Numbers

Sales Drawing	1200980029-000, SD-120098-032
---------------	-------------------------------



EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)*

REACH SVHC

Contained Per - ED/01/2017 (12 January 2017)*
2,4-Di-tert-butyl-6-(5-chlorobenzotriazol-2-yl)p

Halogen-Free

Status

Not Low-Halogen*

For more information, please visit [Contact US](#)

CUST_NOTE	*Product contains part(s) with customer managed
CUST_NOTE1	EHS data. These part(s) are excluded from product compliance status evaluation.
CUST_NOTE2	50 Image
China ROHS	Not Relevant
ELV	Not Contained*
RoHS Phthalates	

Search Parts in this Series

[120098 Series](#)