

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1200878258](#)  
**Status:** **Active**  
**Overview:** [Brad® Nano-Change® &#40;M8&#41; Products](#)  
**Description:** Nano-Change® (M8) Double-Ended Cordset, 3 Poles, Female (Straight) to Male (Straight), 24 AWG, PVC Cable, 1.0m (3.28') Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Industrial Cordsets
Series	<a href="#">120087</a>
Connector End A	Nano-Change® (M8)
Connector End B	Nano-Change® (M8)
IP Rating	IP67
Material - Contact	Copper Alloy
Overview	<a href="#">Brad® Nano-Change® &amp;#40;M8&amp;#41; Products</a>
Product Name	Nano-Change® (M8)
Protocol	N/A
Region	America
Type	Double Ended
UPC	78172554741

**Physical**

Cable Diameter	5.00mm (.197")
Cable Length	1.0m (3.28')
Color - Cable Jacket	Yellow
Coupling Style	Threaded
Gender	Female-Male
Keyway	None
LED Indicator	No
Material - Cable Jacket	PVC
Material - Connector Body	PUR
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Orientation	Straight to Straight
Poles	3
Temperature Range - Operating	-25°C to +80°C
Wire Size AWG	24
Wire/Cable Type	UL 2464

**Electrical**

Current - Maximum per Contact	3.0A
Voltage - Maximum	60V

**Material Info**

Engineering Number	443030E02M010
--------------------	---------------

**Reference - Drawing Numbers**

Sales Drawing	1200878240-000
---------------	----------------



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Not Contained Per - ED/30/2017 (7 July 2017)

**Halogen-Free**

**Status**

**Not Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

**Search Parts in this Series**

[120087](#) Series