

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1300280070](#)  
**Status:** **Active**  
**Overview:** Brad® Mini-Change® Connectors  
**Description:** Micro-Change (M12) Double-Ended Cordset, 5 Poles, Male (90°) to Female (Straight), 22 AWG, DeviceNet Thin Stranded Cable Plus Drain, 1.0m (3.28') Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR6837  
 UL E152210

**General**

Product Family Industrial Cordsets  
 Series [130028](#)  
 Connector End A Micro-Change (M12)  
 Connector End B Micro-Change (M12)  
 IP Rating IP67  
 Material - Contact Copper Alloy  
 Overview [Brad® Mini-Change® Connectors](#)  
 Product Name DeviceNet, Micro-Change (M12)  
 Protocol N/A  
 Region Europe  
 Type Double Ended  
 UPC 78678829128

**Physical**

Cable Diameter 7.24mm (.285")  
 Cable Length 1.0m (3.28')  
 Color - Cable Jacket Gray  
 Coupling Style Threaded  
 Gender Female-Male  
 Keyway Single  
 LED Indicator No  
 Material - Cable Jacket PVC  
 Material - Connector Body PVC  
 Material - Coupling Nut Die-Cast Zinc  
 Material - Plating Mating Gold  
 Orientation 90° to Straight  
 Poles 5  
 Temperature Range - Operating -20°C to +80°C  
 Wire Size AWG 22  
 Wire/Cable Type Shielded-Twisted Pair

**Electrical**


Current - Maximum per Contact 4.0A  
 Voltage - Maximum 250V AC/DC

**Material Info**

Engineering Number DND23A-M010

**Reference - Drawing Numbers**

Sales Drawing SD-130028-007



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS Not Reviewed

ELV Not Reviewed

RoHS Phthalates Not Reviewed

**Search Parts in this Series**

[130028 Series](#)

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**