Part Number : 1200800062
Product Description : Micro-Change (M12) to Ultra-Lock (M12) Double-Ended Cordset, 5 Poles, Male (Straight) to Female (Straight), 22 AWG, PVC Cable, 5.0m (16.40') Length
Series Number : 120080
Status : Obsolete
Product Category : Circular Industrial Cordsets
Engineering Part Number : 8W5030A09M050



Obsolete

Documents and Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Circular Industrial Cordsets
Series	120080
Description	Micro-Change (M12) to Ultra-Lock (M12) Double-Ended Cordset, 5 Poles, Male (Straight) to Female (Straight), 22 AWG, PVC Cable, 5.0m (16.40') Length
IP Rating	IP69K
Product Name	Micro-Change (M12),Ultra-Lock (M12)
Protocol	EtherNet
Type	Double Ended
UPC	78678884954

Agency

CSA	LR6837

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

Physical

Cable Diameter	5.72mm (.225")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Yellow
Connector End A	Micro-Change (M12)
Connector End B	Ultra-Lock (M12)
Coupling Style	Threaded
Gender	Female-Male
Keyway	Single
LED Indicator	None
Material - Cable Jacket	PVC
Material - Connector Body	PVC

Obsolete

Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Orientation	Straight to Straight
Poles	5
Temperature Range - Operating	-25° to +90°C
Wire/Cable Type	UL 2661
Wire Size (AWG)	22

Obsolete