



Part Number : [1200860182](#)

Product Description : Nano-Change (M8) Single-Ended Cordset, 4 Poles, A-Coded, Male (Straight) to Pigtail, 24 AWG, Yellow PVC Cable, 1.0m (3.28') Length

Series Number : 120086

Status : Active

Product Category : Circular Industrial Cordsets

Engineering Part Number : 404006A10M010



Documents and Resources

Drawings

[1200860182_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant with Exemption 3 per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120086
Description	Nano-Change (M8) Single-Ended Cordset, 4 Poles, A-Coded, Male (Straight) to Pigtail, 24 AWG, Yellow PVC Cable, 1.0m (3.28') Length
IP Rating	IP67
Product Name	Nano-Change (M8)
Type	Single Ended
UPC	78678834479

Agency

CSA	LR6837
UL	E152210

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	60V AC / 75V DC

Physical

Cable Diameter	4.57mm (.180")
Cable Length	1.0m (3.28')
Color - Cable Jacket	Yellow
Connector End A	Nano-Change (M8)
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Male-Pigtail

Keyway	A-Coded
LED Indicator	None
Material - Cable Jacket	PVC
Material - Connector Body	TPE
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	112.000/g
Orientation	Straight to Pigtail
Poles	4
Temperature Range - Operating	-20° to +105°C
Wire/Cable Type	UL 2661
Wire Size (AWG)	24