



Part Number : [1200730335](#)

Product Description : Micro-Change (1/2"-20 UNF) Double-Ended Cordset, 5 Poles, C-Coded, Male (Straight) to Female (90°), 22 AWG, PVC Cable, 0.91m (3.0') Length

Series Number : 120073

Status : Active

Product Category : Circular Industrial Cordsets

Engineering Part Number : 775031D02F030



Documents and Resources

Drawings

[1200730335_sd.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120073
Description	Micro-Change (1/2"-20 UNF) Double-Ended Cordset, 5 Poles, C-Coded, Male (Straight) to Female (90°), 22 AWG, PVC Cable, 0.91m (3.0') Length
IP Rating	IP67
Product Name	Micro-Change (1/2" - 20 UNF)
Protocol	PROFIBUS
Type	Double Ended
UPC	78678850659

Agency

CSA	LR6837
UL	E152210

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

Physical

Cable Diameter	5.72mm (.225")
Cable Length	0.91m (3.0')
Color - Cable Jacket	Yellow
Connector End A	Micro-Change (1/2" - 20 UNF)
Connector End B	Micro-Change (1/2" - 20 UNF)
Coupling Style	Threaded
Gender	Female-Male
Keyway	C-Coded

LED Indicator	None
Material - Cable Jacket	PVC
Material - Connector Body	PVC
Material - Contact	Copper Alloy
Material - Coupling Nut	Black Epoxy Coated Zinc
Material - O-Ring	Nitrile Rubber
Material - Plating Mating	Gold
Orientation	90° to Straight
Poles	5
Temperature Range - Operating	-20° to +105°C
Wire/Cable Type	UL 2661
Wire Size (AWG)	22