



Part Number : [1200868548](#)

Product Description : Nano-Change (M8) Double-Ended Cordset, 4 Poles, A-Coded, Male (Straight) to Female (Straight), 22 AWG, Yellow TPE Cable, 2.0m (6.56') Length

Series Number : 120087

Status : Active

Product Category : Circular Industrial Cordsets

Engineering Part Number : 444030K05M020



Documents and Resources

Drawings

[1200868548_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant with Exemption 3 per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120087
Description	Nano-Change (M8) Double-Ended Cordset, 4 Poles, A-Coded, Male (Straight) to Female (Straight), 22 AWG, Yellow TPE Cable, 2.0m (6.56') Length
IP Rating	IP67
Product Name	Nano-Change (M8)
Protocol	N/A
Type	Double Ended
UPC	78172540911

Agency

UL	E152210
----	---------

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	60V AC / 75V DC

Physical

Cable Diameter	5.08mm (.200")
Cable Length	2.0m (6.56')
Color - Cable Jacket	Yellow
Connector End A	Nano-Change (M8)
Connector End B	Nano-Change (M8)
Coupling Style	Threaded

Gender	Female-Male
Keyway	A-Coded
LED Indicator	None
Material - Cable Jacket	TPE
Material - Connector Body	Thermoplastic Elastomer
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	111.000/g
Orientation	Straight to Straight
Poles	4
Temperature Range - Operating	-25° to +80°C
Wire/Cable Type	PLTC/ITC
Wire Size (AWG)	22