

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200895011](#)
Status: **Active**
Overview: [Brad Nano-Change \(M8\) Products](#)
Description: Y Nano-Change (M8) Splitter to Nano-Change (M8) 3 Pole Female to 3 Pole Male

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family Industrial Tees and Splitters
 Series [120089](#)
 IP Rating IP67
 Overview [Brad Nano-Change \(M8\) Products](#)
 Product Name Nano-Change (M8)
 Type Splitter - Solid Body
 UPC 883906783952

Physical

Drop Connector Nano-Change (M8)
 Drop Gender Male
 Keyway None
 Left Trunk Connector Nano-Change (M8)
 Left Trunk Gender Female
 Leg 1 Length N/A
 Leg 2 Length N/A
 Material - Cable Jacket N/A
 Material - Connector Body PUR
 Material - Coupling Nut Nickel-plated Brass
 Net Weight 1.000/g
 Poles 4
 Right Trunk Connector Nano-Change (M8)
 Right Trunk Gender Female
 Temperature Range - Operating -20°C to +90°C

Electrical

Current - Maximum per Contact 4.0A
 Voltage - Maximum 60V AC / 75V DC

Material Info

Engineering Number 0808 03LMF 00000

Reference - Drawing Numbers

Sales Drawing SD-120089-002-001

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2021)4569-DC (8 July 2021)

Lead

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT_CE -

Declaration of

Conformity

China RoHS

50 Image

Not Relevant

Not Contained

CER_4000380987_00_000.pdf

Search Parts in this Series

[120089](#) Series