



**Part Number :** [1204061033](#)

**Product Description :** Ultra-Lock 2.0 (M12) Double-Ended Cordset, 4 Poles, D-Coded, Male (90°) to Male (90°), PROFINET Cat5e PUR Cable, Green, 1.0m Length

**Series Number :** 120406

**Status :** Active

**Product Category :** Circular Industrial Cordsets

**Engineering Number :** EYYAS6312M010



---

## Documents & Resources


### Drawings

[1204061033\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead; Lead monoxide per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

## Part Details

### General

Status	Active
Category	Circular Industrial Cordsets
Series	120406
Description	Ultra-Lock 2.0 (M12) Double-Ended Cordset, 4 Poles, D-Coded, Male (90°) to Male (90°), PROFINET Cat5e PUR Cable, Green, 1.0m Length
IP Rating	IP67, IP69K
Performance Category	5e
Product Name	Ultra-Lock 2.0 (M12),Industrial Ethernet
Protocol	PROFINET
Type	Double Ended
UPC	196823153648

### Agency

UL	E361772
----	---------

### Electrical

Current - Maximum per Contact	4A
Voltage - Maximum	250V

### Physical

Cable Diameter	6.80mm (.268")
Cable Length	1.0m (3.28')
Color - Cable Jacket	Green
Connector End A	Ultra-Lock 2.0 (M12)
Connector End B	Ultra-Lock 2.0 (M12)
Coupling Style	Push to Lock
Gender	Male-Male
Keyway	D-Coded

LED Indicator	None
Material - Cable Jacket	PUR
Material - Connector Body	TPC
Material - Contact	Brass
Material - Coupling Nut	N/A
Material - Plating Mating	Gold
Net Weight	108.658/g
Orientation	90° to 90°
Poles	4
Temperature Range - Operating	-40° to +85°C
Wire/Cable Type	UL 21215
Wire Size (AWG)	22

---

---

This document was generated on Apr 07, 2025