



Part Number : [1205010113](#)
Product Description : Micro-Change (M12) Double-Ended Cordset, 5 Poles, L-Coded, Female (90°) to Male (Straight), 14 AWG, Gray TPU WSOR Cable, 10.0m (32.81') Length
Series Number : 120501
Status : Active
Product Category : Circular Industrial Cordsets
Engineering Part Number : LLP5031B63M100



Documents & Resources

Drawings

- [1205010113_sd.pdf](#)
- [1205010169-K00.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant with Exemption 3 per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120501
Description	Micro-Change (M12) Double-Ended Cordset, 5 Poles, L-Coded, Female (90°) to Male (Straight), 14 AWG, Gray TPU WSOR Cable, 10.0m (32.81') Length
IP Rating	IP67
Product Name	Micro-Change (M12)
Type	Double Ended
UPC	193264522736

Agency

UL	E152210
----	---------

Electrical

Current - Maximum per Contact	16.0A
Voltage - Maximum	63V AC/DC

Physical

Cable Diameter	11.30mm (.445")
Cable Length	10.0m (32.81')
Color - Cable Jacket	Gray
Connector End A	Micro-Change (M12)

Connector End B	Micro-Change (M12)
Coupling Style	Threaded
Gender	Female-Male
Keyway	L-Coded
LED Indicator	None
Material - Cable Jacket	WSOR TPU
Material - Connector Body	TPE
Material - Contact	Brass
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	FKM
Material - Plating Mating	Gold
Orientation	90° to Straight
Poles	5
Temperature Range - Operating	-25° to +85°C
Wire/Cable Type	UL 21215
Wire Size (AWG)	14