



Part Number : 1300128039

Product Description : Mini-Change C-Size Double-Ended Cordset, 12 Poles, Male (Straight) to Female (Straight), 19/22 AWG, Black TPU Cable, 10.0m (32.81') Length

Series Number : 130012

Status : Active

Product Category : Circular Industrial Cordsets

Engineering Number : 332130B80M100

Documents & Resources

Drawings

Drawing 1300128039_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Reviewed per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	130012
Description	Mini-Change C-Size Double-Ended Cordset, 12 Poles, Male (Straight) to Female (Straight), 19/22 AWG, Black TPU Cable, 10.0m (32.81') Length
IP Rating	IP67
Product Family	Brad Mini-Change Connectors
Product Name	Mini-Change
Region	Asia
Type	Double Ended
UPC	889056054867

Electrical

Current - Maximum per Contact	5.0A
Voltage - Maximum	600V

Physical

Cable Diameter	8.50mm (.335")
Cable Length	10.0m (32.81')
Color - Cable Jacket	Black
Connector End A	Mini-Change
Connector End B	Mini-Change
Coupling Style	Threaded
Gender	Female-Male
Keyway	Single
LED Indicator	No
Material - Cable Jacket	TPU
Material - Connector Body	TPE
Material - Contact	Brass
Material - Coupling Nut	Nickel-plated Zinc Alloy
Material - Plating Mating	Gold
Net Weight	1201.000/g

Orientation	Straight to Straight
Poles	12
Temperature Range - Operating	-40° to +90°C
Wire/Cable Type	UL 21215
Wire Size (AWG)	19, 22

This document was generated on Jul 03, 2024