



**Part Number :** [1200010722](#)

**Product Description :** Micro-Change (M12) Single-Ended Cordset, 4 Poles, Female (90°) to Pigtail, 20 AWG, 5.0m (16.40') Length

**Series Number :** 120001

**Status :** Obsolete

**Product Category :** Circular Industrial Cordsets

**Engineering Number :** 804001J11M050



---

## Documents & Resources

### Drawings

[1200010722 sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

## Part Details

### General

Status	Obsolete
Category	Circular Industrial Cordsets
Series	120001
Description	Micro-Change (M12) Single-Ended Cordset, 4 Poles, Female (90°) to Pigtail, 20 AWG, 5.0m (16.40') Length
IP Rating	IP67, IP68
Product Name	Micro-Change (M12)
Type	Single Ended
UPC	883906487867

### Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

### Physical

Cable Diameter	6.10mm (.240")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Gray
Connector End A	Micro-Change (M12)
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	Single
LED Indicator	None
Material - Cable Jacket	PVC
Material - Connector Body	PVC
Material - Contact	Copper Alloy
Material - Coupling Nut	Teflon Nickel-plated Brass
Material - O-Ring	Viton

Material - Plating Mating	Gold
Net Weight	308.247/g
Orientation	90° to Pigtail
Poles	4
Temperature Range - Operating	0° to +75°C
Wire/Cable Type	Unshielded PVC
Wire Size (AWG)	20

---

This document was generated on Oct 02, 2025

Obsolete