




Type of Screw and Gasket
see sheet 2, PN KEY





Face View
(see Insert Orientation)



INSERT ORIENTATION	
Housing 2 Poles + 2 Earths	Housing 3 Poles + 1 Earth
Earth H6/H12 - Not Used E451XXXXXX1XXXX	Earth H12 -Not Used E451XXXXXX2XXXX PIN 3 Not Used
Earth H3/H9 - Not Used E451XXXXXX4XXXX	Earth H3 - Not Used E451XXXXXX3XXXX PIN 3 Not Used
Earth H6/H12 - Not Used E451XXXXXX1XC3X E451XXXXXX1XC7X E451XXXXXX1XR0X E451XXXXXX1XR2X	Earth H6 - Not Used E451XXXXXX6XXXX PIN 3 Not Used
Insert 180°	Earth H9 - Not Used E451XXXXXX9XXXX PIN 3 Not Used

Type of Screws and Gaskets






Profiled Gasket	Flat Gasket	Integrated Gasket	Screw M3x25
			
			Screw M3x27 + Washer
			

TABLE OF LENGTH TOLERANCES [mm]		
Over	Up to and Including	Tolerance
0	1000	±20
1000	3000	±30
3000	5000	±40
5000	10000	±50
10000	15000	±100
15000	20000	±150
20000		±L/100

DOCUMENT STATUS	P1	RELEASE DATE	2024/07/04 12:12:01

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

SYMBOLS: = 0

DIMENSION UNITS: mm | SCALE: 1:1

GENERAL TOLERANCES (UNLESS SPECIFIED)

ANGULAR TOL	±	1.0 °
4 PLACES	±	
3 PLACES	±	
2 PLACES	±	0.05
1 PLACE	±	0.3
0 PLACES	±	0.5

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

CURRENT REV DESC:

EC NO: 791448
DRWN: MARCIM6 2024/06/28
CHK'D: RSILLER 2024/07/04
APPR: RSILLER 2024/07/04

INITIAL REVISION:
DRWN: SSM 2019/06/04
APPR: RSILLER 2019/06/28

THIRD ANGLE PROJECTION | DRAWING: A3-SIZE | SERIES: 121050

molex

STANDARD E451 DIN FORM A
EN 175301-803

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION
1210504000	PSD	000	A1

MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
SEE 1210504000_PDP	GENERAL MARKET	1 OF 3

FORMAT: molex B size A3
REVISION: H
DATE: 2018/01/16

KLUCZ / PN KEY ENGINEERING PN

E	4	5	1	X	X	X	X	X	X	X	X	X	X	X

E - Packing without bag
W - Single Packing

Number of wires:
1 - 2 Wires

Cable type:
See Table

Head Colour:
G - Grey
N - Black
A - CSA-UL Black
B - CSA-UL Grey

Cable Length in[cm]
050 = 50cm
300 = 300cm
10K = 1000cm

Earth PIN location (see insert orientation table):
1 = Double Earth on H6 & H12
2 = Earth on H12
3 = Earth on H3
4 = Double Earth on H3 & H9
6 = Earth on H6
9 = Earth on H9

Wiring Configuration:
See sheet 3

Voltage and LED Colour

Red LED	Green LED	Yellow Led
1 = 12V	A = 12V	G = 12V
2 = 24V	B = 24V	H = 24V
3 = 48V	C = 48V	K = 48V
4 = 115V	D = 115V	L = 115V
5 = 230V	E = 230V	M = 230V

Type of Gasket and Screw (see sheet 1):
1 = NBR Profile Gasket + Fixing Screw M3x25mm
2 = NBR Flat Gasket + Fixing Screw M3x25mm
3 = Silicone Profile Gasket + Fixing Screw M3x25mm
4 = Silicone Flat Gasket + Fixing Screw M3x25mm
P = NBR Integrated Gasket + Fixing Screw with Washer M3x27mm Assembled on Connector
R = NBR Integrated Gasket + Fixing Screw with Washer M3x27mm NOT Assembled on Connector
T = NBR Profile Gasket + Fixing Screw with Washer M3x27mm

CABLE LIST

CABLE TYPE	NO. OF WIRES	CROSS SECTION	CABLE O.D.	CABLE JACKET	KOLORY PRZEWODÓW WIRES COLOR	SHIELD
A2	2	AWG 20	5.4mm±0.2	PVC BLACK	BN, BU	-
A3	2	AWG 18	6.2mm±0.25	PVC BLACK	BN, BU	-
B2	2	AWG 20	5.6mm±0.2	PUR BLACK	BN, BU	-
B3	2	AWG 18	6.2mm±0.2	PUR BLACK	BN, BU	-
I2	2	0.5mm²	5.5mm+0.3	PVC GREY	BN, BU	-
I3	2	0.75mm²	5.5mm±0.2	PVC GREY	BK1,BK2	-
I4	2	1mm²	7.1mm±0.2	PVC GREY	BN, BU	-
N2	2	0.5mm²	5.25mm±0.65	PVC BLACK	BN, BU	-
N3	2	0.75mm²	6.45mm±0.75	PVC BLACK	BN, BU	-
N4	2	1mm²	6.45mm±0.75	PVC BLACK	BN, BU	-
P2	2	0.5mm²	5.5mm+0.2	PUR BLACK	BN, BU	-
P3	2	0.75mm²	6.5mm±0.2	PUR BLACK	BN, BU	-
W2	2	0.5mm²	~5.2mm	WSOR BLACK	BN, BU	-
W3	2	0.75mm²	~6.0mm	WSOR BLACK	BN, BU	-

Notes:
1. Please see excel sheet 1210504000_PDP for currently configured part numbers.
2. Drawing is a replacement for: SD-121050-004

DOCUMENT STATUS	P1	RELEASE DATE	2024/07/04 12:12:01

FORMAT: marcim Standard A3
REVISION: H
DATE: 2018/01/16

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

SYMBOLS: A = 0, B = 0, C = 0, D = 0, E = 0, F = 0, G = 0, H = 0

DIMENSION UNITS: mm
SCALE: 1:1

GENERAL TOLERANCES (UNLESS SPECIFIED)
ANGULAR TOL ± 1.0°
4 PLACES ±
3 PLACES ±
2 PLACES ± 0.05
1 PLACE ± 0.3
0 PLACES ± 0.5
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

CURRENT REV DESC:

EC NO: 791448
DRWN: MARCIM6 2024/06/28
CHK'D: RSILLER 2024/07/04
APPR: RSILLER 2024/07/04

INITIAL REVISION:
DRWN: SSM 2019/06/04
APPR: RSILLER 2019/06/28

THIRD ANGLE PROJECTION
DRAWING: A3-SIZE
SERIES: 121050

molex

STANDARD E451 DIN FORM A
EN 175301-803


PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION
1210504000	PSD	000	A1


MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
SEE 1210504000_PDP	GENERAL MARKET	2 OF 3

WIRING DIAGRAMS


ELECTRICAL DIAGRAM 00
WITHOUT LED




ELECTRICAL DIAGRAM A1




ELECTRICAL DIAGRAM C3




ELECTRICAL DIAGRAM C4




ELECTRICAL DIAGRAM C7




ELECTRICAL DIAGRAM D0




ELECTRICAL DIAGRAM E0




ELECTRICAL DIAGRAM R0




ELECTRICAL DIAGRAM R2




ELECTRICAL DIAGRAM S0



ELECTRICAL DIAGRAM S1



ELECTRICAL DIAGRAM S3



SYMBOLS	
E/A = 0	
E/C = 0	
E/B = 0	
S = 0	
▼ = 0	
C = 0	
☒ = 0	
■ = 0	
▽ = 0	

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS	SCALE
mm	1:1

GENERAL TOLERANCES (UNLESS SPECIFIED)

ANGULAR TOL	±	1.0 °
4 PLACES	±	
3 PLACES	±	
2 PLACES	±	0.05
1 PLACE	±	0.3
0 PLACES	±	0.5

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

CURRENT REV DESC:

EC NO: 791448
DRWN: MARCIM6 2024/06/28
CHK'D: RSILLER 2024/07/04
APPR: RSILLER 2024/07/04

INITIAL REVISION:
DRWN: SSM 2019/06/04
APPR: RSILLER 2019/06/28

molex

STANDARD E451 DIN FORM A
EN 175301-803

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION
1210504000	PSD	000	A1

THIRD ANGLE PROJECTION	DRAWING	SERIES
	A3-SIZE	121050

MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
SEE 1210504000_PDP	GENERAL MARKET	3 OF 3

DOCUMENT STATUS	P1	RELEASE DATE	2024/07/04 12:12:01

FORMAT: master_Sheet-A3
REVISION: H
DATE: 2018/01/16