

## Cable glands Progress® stainless steel A2 for high temperature applications



### Long entry thread metric

#### Type approval: Progress S2 HT

- One-piece sealing insert
- not overall length insulated

<b>Order number:</b>	<b>1100.25.96.205</b>
E-No:	121613608
EAN:	7611614133751
Material	CrNi stainless steel A2 (DIN EN 1.4305 / AISI 303)
Identification	1 groove
Seal	FPM
O-ring	FPM
Operation temperature	-40°C / +200°C
Strain relief	Version A acc. to EN 62444
Protection class	IP 68 (up to 10 bar) / IP 69
Entry thread	M25x1.5
Clamping range without insert min.	16.0 mm
Clamping range without insert max.	20.5 mm
Wrench size	30 mm
Dimension H	25 mm
Thread length L	11 mm
Dispatch	25

1 = Metric coarse-pitch thread (with VDE test report)