



Klemsan®

430012 SK 2

SK 2

| | | |
|------------------------------------|------------------------------------|-------------------------|
| General Product Information | Insulating material | PA |
| | Inflammability class acc. to UL 94 | V2 |
| | Packing Unit | — |
| | Weight (g) | — |
| | Continuous Operating Temp. | (min.-max.) |
| | DIN-EN 45545Z | |
| VDE Technical Data | Nominal Voltage | 450 V ~ |
| | Nominal Current | 41 A |
| | Cross Section | 4 mm ² |
| | VDE Norm | IEC 60998-1/IEC 60998-2 |
| UL / CSA Technical Data | Nominal Voltage | 300 V ~ |
| | Nominal Current | 30 A |
| | Cross Section | AWG/22-10 |
| Connection Data | Minimum solid strand cross section | 0.75 mm ² |
| | Maximum solid Strand cross section | 6 mm ² |
| | Minimum fine Strand cross section | 0.5 mm ² |
| | Maximum fine strand cross section | 4 mm ² |
| | AWG Conductor Range | 22-10 |
| | Connection Type | screw/vidalı |
| | Insulation Stripping length | 8 mm |
| SK Dimensions | Tightening torque | 0.5 Nm |
| | L | 116 |
| | W | 19 |

Declaration of Conformity - Declaration of Conformity Certificate

LAPEM - RETIE Sertifikası - LAPEM - Retie Certificate

Ukrayna Uygunluk Sertifikası - Ukrayna Uygunluk Sertifikası

Order Info



430012 SK 2



431012 SK 2