


Cable glands Progress® EMC Series 85 nickel-plated brass with collet chuck



Entry thread metric

Type approval: Progress EMV Serie 85

- Two-piece sealing insert
- not overall length insulated

Order number:	1000.32.85.220
E-No:	121132818
EAN:	7611614217796
Material	Nickel-plated brass
Seal	TPE
O-ring	NBR
Operation temperature	-40°C / +100°C
Strain relief	Version A acc. to EN 62444
Protection class	IP 68 (up to 10 bar) / IP 69
Properties	For high leakage currents, concentric shield contact with minimal transfer resistances and transfer impedances
Entry thread	M32x1.5
Clamping range with insert min.	17.0 mm
Clamping range with insert max.	21.0 mm
Clamping range without insert min.	21.0 mm
Clamping range without insert max.	25.5 mm
Cable shield diameter	14.0-22.0
Wrench size	36 mm
Dimension H	66 mm
Thread length L	10 mm
Dimension x	24
Dispatch	25

Available with sealing inserts conformity with EN 45545 / NFPA 130. When placing an inquiry, prefix the article number by the capital F.

Important: To provide the best possible protection for the cable shield and the cable, it is necessary to install a copper EMC tape.